



Catalog No. TY244M

Description: CABLE TIE 30LB 14.5IN NAT NYLON

UPC No 5414363062004

Home > Wire & Cable Management > Ty-Rap > Cable ties

Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 366mm (14.4 Inches), Width of 3.6mm (0.14 Inch), Thickness of 1mm (0.04 Inch), Tensile Strength Rating of 134 Newtons (30 Pounds), Bulk Pack

Descriptors

Category	Cable ties
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.

Specifications

Material	Nylon/Polyamide 6.6
Color	Natural
Lock Mechanism	Stainless Steel Barb
Tensile Strength	30 pounds , 134 newtons

Classifications

Brand Name	Ty-Rap
Standard	UL E49405

Dimensions

Width	0.14 in , 3.6 mm
Length	14.4 in , 366 mm
Thickness	0.04 in , 1.0 mm
Bundle Diameter	0.08 to 4.02 in , 2 to 102 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant
TSCA	TSCA Section 6(h) Compliant
POPs	POPs 28 Compliant

ETIM	EC000046 Cable tie
Band width	3.6 mm
Length belt/tape/tie	366 mm
Length belt/tape/tie	14.4 inch
Tie thickness	1 mm
Tie thickness	0.04 inch
Max. bundle diameter	102 mm
Min. holding force	134 N
Operation temperature	-40-+85 °C
Operation temperature	-40-+185 °F
Model	Internal tothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide (PA)
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	Y
Colour	Natural colour
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
VG approval	N
MIL approval	N
UL approval	Y

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
CSA	2884	441406	N/A	1349334_2014-11-06	N/A
UL	E49405	N/A	ZODZ	N/A	N/A