



Part Number : [1202530149](#)
Product Description : Contrinex Inductive Sensor,
M12 Housing, 0 - 6mm Operating Distance, Quasi-
embeddable, Analog, 0 - 10V Output, 4-pin M12
Connector, 60mm Housing Length
Series Number : 120253
Status : Not Recommended For New Design
Product Category : Inductive and Photoelectric
Sensors
Engineering Number : DW-AS-509-M12-390



Documents & Resources

Specifications

[1202530146-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Not Recommended For New Design
Category	Inductive Sensors
Series	120253
Description	Contrinex Inductive Sensor, M12 Housing, 0 - 6mm Operating Distance, Quasi-embeddable, Analog, 0 - 10V Output, 4-pin M12 Connector, 60mm Housing Length
IP Rating	IP67
Product Name	Contrinex
Type	Inductive
UPC	191130063192

Electrical

Output	0-10V
Polarity	Analog

Physical

Connection	Connector (M12, 4-pin)
Length	60mm
Material - Housing	Chrome Plated Brass
Material - Sensing Face	PBTP
Mounting Style	Quasi-embeddable
Operating Distance	0 - 6mm
Output	0-10V

Sensor Housing Size	M12
Temperature Range - Operating	-25° to +70°C

This document was generated on Sep 14, 2025