



CABLE OUTER CONDUCTOR: COPPER WIRE BRAID, TIN PLATING


REV	DESCRIPTION	DATE	ECN	APPR
G	REDRAWN, GOLD PLATING WAS SILVER PLATING; OLD PN "A-IPAG" COMBINED TO "A-IPA-" ; NO "A-IPAG" FOR NEW PN	08-Jan-19	10390	JTS



CABLE ASSEMBLY OVERALL LENGTH TOLERANCE	
OVERALL LENGTH L (mm)	STANDARD TOLERANCE (mm)
20 ≤ L < 35	± 2
35 ≤ L < 200	± 4
200 ≤ L < 500	± 8
500 ≤ L < 1000	± 12
1000 ≤ L	±1.5 %



SCALE 8.000



A - I PAX I 37 - XXXYZ

EXAMPLE : 1020 = 1020MM

N=BROWN

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm 0.5 - 6mm 6 - 30mm 30 - 120mm ANGLES ± 0.05mm ±0.1mm ±0.2mm ± 0.3mm ±1°					MATERIAL		DRAWN		DATE		TITLE AMC PLUG TO AMC PLUG JUMPER ASSEMBLY ON 1.37MM CABLE				Amphenol RF www.amphenolrf.com			
NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.							JEKY		29-Jan-19									
					REFERENCE		ENGINEER		DATE									
							FIGO		29-Jan-19									
REF:					APPROVED		DATE		SCALE: 3.0:1.0 SHEET 2 OF 2				DRAWING NO. A-IPAX137-XXXXYZ					
					FIGO		12-Feb-19						ITEM NO. A-IPAX137-XXXXYZ					
CONFIGURATION LEVEL: In Work					CAD FILE		DWG SIZE				REV				PART NO. A-IPAX137-XXXXYZ			
FINISH							B				G							