





REV.	DATE	DESCRIPTION
A	01/30/04	UPDATE DRAWING FORMAT
B	05/22/05	MODIFY PLATING SPEC
C	07/08/07	REVISE STRIPPING DIMS AND FERRULE



RECOMMENDED
CABLE STRIPPING DIM'S



- NOTE:
1. CRIMPED FERRULE HEX CRIMP SIZE .429"
 2. CRIMPED CONTACT PIN HEX CRIMP SIZE .100"

				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”	APPROVALS	DATE	Amphenol Connex					
8					DRAWN	G.R.S.						07/08/07
7					CHECKED							
6					ISSUED			PART DESCRIPTION N CRIMP PLUG (FOR RG-214/U CABLE)				
5	FERRULE	COPPER	NECOTE		1	SHEET	1 OF 1					
4	CONTACT PIN	BRASS	GOLD		1			PART NO. 172166				
3	INSULATOR	TEFLON	NATURAL		1							
2	BARREL	BRASS	NEXCOTE		1			DWG. NO. 172166.DWG				
1	BODY	BRASS	NEXCOTE		1							
DESCRIPTION					MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING				
				CAD FILE		C:/172/172166.DWG						