




Application Tooling > Insertion & Extraction Tools



Insertion & Extraction Tool Type: **Contact Extraction**

Insertion & Extraction Tool Application: **Contact-to-Housing**

Features

Product Type Features

Insertion & Extraction Tool Type	Contact Extraction
Insertion & Extraction Tool Application	Contact-to-Housing

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5-163083-1
.062 DIA SOC.ASS.3+

TE Part # 164160-6
.062 DIA PIN ASS.3+

TE Part # 1-163083-0
.062 DIA SOC.ASS.3+

TE Part # 1-163089-0
SPECIAL PLATED

TE Part # 3-1105001-5
HD.M-C-BU.AU.0,8

TE Part # 164159-2
M-SRS PIN ASSY 3+

TE Part # 164161-6
.062 PIN ASSY.3+

TE Part # 1-163091-0
SPECIAL PLATED

TE Part # 1-164161-2
.62 DIA SOCKET PIC


TE Part # 1-66598-5
III+ SKT,18-14,30AU/FL,STRIP



TE Part # 5-163085-2
.062 PIN, TYPE III Contact



TE Part # 163081-1
.062 DIA PIN ASSY 3+



TE Part # 164164-1
PIN ASS



TE Part # 164163-4
TYPE 3+ STIFT






TE Part # 66098-7
III+ PIN,18-16,TIN-LEAD,STRIP






TE Part # 66360-8
III+ SKT,18-14,30AU/FL,LP



Also in the Series | AMP Type II



Also in the Series | AMP Type III+



Customers Also Bought





TE Part #206044-1
CPC PLUG ASSEMBLY SIZE 17-14




TE Part #206429-1
CPC PLUG ASSY, 11-4, REV SEX




TE Part #2063388-1
TOOL, EXTRACTION



TE Part #2311162-4
DYNAMIC D-3 FMLB REC CONT AU0.
38 2L L/P



TE Part #1SNS421282Z0000
BTD0000257215- (Terminal block B231)



TE Part #91002-1
TOOL SMALL WIRE INS

Documents

Product Drawings

[EXTRACT TOOL TYPE 2 20-16](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals

[CSA Certificate](#)

English