
Part Number : 2262031082
Product Description : OneBlade-to-OneBlade Off-the-Shelf (OTS) Cable Assembly, 1.00mm Pitch, Single Row, 150.00mm Length, Tin (Sn) Plating, 8 Circuits, Black
Series Number : 226203
Status : Active
Product Category : Power and Signal Cable Assemblies



Documents and Resources

Drawings

2262031082_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

Downloaded from Arrow.com.

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	226203
Description	OneBlade-to-OneBlade Off-the-Shelf (OTS) Cable Assembly, 1.00mm Pitch, Single Row, 150.00mm Length, Tin (Sn) Plating, 8 Circuits, Black
Application	Wire-to-Board
Assembly Configuration	Dual Ended Connectors
Connector to Connector	OneBlade-to-OneBlade
Product Name	OneBlade
Type	Discrete Wire Assembly
UPC	198282227526

Electrical

Current - Maximum per Contact	2.5A
Voltage - Maximum	100V AC (RMS)/DC

Physical

Cable Length	150.00mm
Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	Black
Gender	Female-Female

Downloaded from Arrow.com.

Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Resin	Polyamide (PA)
Net Weight	2.027/g
Number of Rows	1
Packaging Type	Bag
Pitch - Mating Interface	1.00mm
Plating min - Mating	1.000µm
Plating min - Termination	1.000µm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 10125
Wire Size (AWG)	28

Downloaded from Arrow.com.