OMRON Industrial Automation



MY2-GS-R DC12 BY OMZ

Relay, plug-in, 8-pin, DPDT, 10 A, mechanical indicator, 12 VDC

Downloaded from Arrow.com.

Specifications

Mounting method	With plug-in socket
Usage	General purpose
Poles	2
Rated carry current	10 A
Coil voltage	12 V
Operation voltage	DC
Contact material	Ag
Contact description	DPDT
Features	Transparent case, With mechanical indicator
Terminal type	Plug-in, Solder

Downloaded from Arrow.com.

Fits to



PY08-02
Socket, back-connecting, 8-pin, PCB terminals



PYF-08-PU BY OMB
Socket, DIN rail/surface mounting, 31 mm, 8-pin, Push-in terminals



PYF-08-PU-L BY OMB
Socket, DIN rail/surface mounting, 31 mm, 8-pin, Push-in terminals



PYF08A-N BY OMZ
Socket, DIN rail/surface mounting, 8-pin, screw terminals (IEC/VDE)



PYF08S BY OMZ
Socket, DIN rail mounting, 8-pin, screwless terminals



PYFZ-08-E BY OMZ
Socket, DIN rail/surface mounting, 8-pin, screw terminals (standard)

Downloads



Industrial Relays
Brochure
EN PDF 2.77 MB



MY-GS-R/MY(s)/MYK/MYQ/MYH Miniature Power Relays
Datasheet
EN PDF 20.3 MB



OMRON Manufacturing Know-How: High Quality Relays
Leaflet
EN PDF 449 KB



Panel Building
Brochure
EN PDF 3.11 MB



Solution case study No.8 Environment resistance
Brochure
EN PDF 623 KB

Downloaded from Arrow.com.

TERMS OF WEBSITE USE

This PDF document was created from the European OMRON Industrial Automation website on 7 August, 2026. Click here for terms of use.

INDUSTRIAL AUTOMATION | INDUSTRIAL.OMRON.EU

Downloaded from Arrow.com.