

© 2023 TE Connectivity. All Rights Reserved.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	K5	SUPERSEDED 234235-E	04AUG2026	SA	LET








CONSIDER MOUNTING POSITION: SMALL PEG RIGHT


TAPE ON REEL PACKAGING ACCORDING TO DIN IEC 60286-3
PACKAGING UNIT: 80 PCS














1. DRAWING SPECIFICATION ACCORDING TO 5_3_16-DOC-1806-00915
2. COPLANARITY AREA OF TERMINATION □ 0,1MM
3. PART; 100 PCS. IN BUBBLE BAGS/BULK




PCB-LAYOUT PROPOSAL



DETAIL X
SCALE 10:1



SCALE 2:1



3D VIEW

3				
SUPERSEDED	SUPERSEDED			
-	1	-	TAPE AND REEL	6
-	1	-	HOOD	5
1	1	-	SOLDER CLIP LEFT	4
1	1	-	SOLDER CLIP RIGHT	3
4	4	-	PINS	2
1	1	-	M8 HOUSING	1
234235-E	224152-E	REV	DESCRIPTION	ITEM NO.
-	-	REV OF EACH ASSY NO. (WHEN BLANK, USE DWG. REV)		
QTY		PARTS LIST		

V= TURNED CONTACT (PCB SIDE CAN BE USED WITH POTTING COMPOUND)

INSPECTION LEVEL 1: CONTROL CHART REQUIRED
(1) PROOF OF PROCESS CAPABILITY OR 100% TEST IF PROCESS CAPABILITY IS NOT ACHIEVED

INSPECTION LEVEL 2 AND 3: CONTROL CHART REQUIRED
(2) PROOF OF MEAN VALUE, STANDARD DEVIATION AND MACHINE CAPABILITY

(3) PROOF OF VALUES OR PROOF OF ATTRIBUTIVE TEST

INFORMATION ON THE SCOPE OF TESTING AND DETECTION BY ERNI VA 7.3.2.3

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED: DIM. FOR INFORMATION ISO 8015
0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

MATERIAL: -
FINISH: -

DWN B S ADRUSH 21AUG2023
CHK M SZELAG 23AUG2023
APVD J DE BRUIJN 23AUG2023
PRODUCT SPEC 108-94887
APPLICATION SPEC 114-94781
WEIGHT -

TE Connectivity

NAME M8 CIRCULAR CONNECTOR
MALE CONNECTOR 4P 16.25 SMT V
-

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-224152-E	-

CUSTOMER DRAWING | SCALE 5:1 | SHEET 1 OF 1 | REV K5

1471-9 (3/13)

Downloaded from Arrow.com.