


Copyright FCI.


FCIconnect.com

PRODUCT NUMBER	PITCH
KUxxC1x100J0G	15.00 mm









RECOMMENTED P.C.B LAYOUT
TOP VIEW

Material:
- Item ⓐ Terminal housing:Thermoplastic(UL94V-0)
- Item ⓑ Male contact: Copper. Gold plated.
- Item ⓒ With flange nut: Steel M5.0 zinc plated.

Electrical: cULus
- Voltage rating: 600 V
- Current rating: 115 A
- Withstanding Voltage: 2.2 KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: c UL us

Dim L=N×15.00+24.4
Dim P=(N-1)×15.00
Dim E=(N-1)×15.00+29.0

N=Number of poles

Poles	Tolerance
2p-4p	±0.20
5p-7p	±0.35
8p-10p	±0.50

PART NO.: KU xx C 1 x 1 00J0 G

		Color	
Solid block	0	Black (RAL9005)	RoHS compliant (lead<4%) In copper Alloy
No. of poles	2	Red (RAL3001/D)	
02 2 poles	3	Orange(RAL2011/P)	
03 3 poles	4	Yellow(RAL1018/A)	
... ...	5	Green(RAL6018/T)	
10 10 poles	6	Blue (RAL5015/A)	
	8	Grey(RAL7035/D)	
	9	White(RAL1102)	
	C	Green(RAL6018/U)	

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family: TERMINAL BLOCK
ltr	ecn no	dr	date	tolerances unless otherwise specified			title: TERMINAL BLOCK PLUGGABLE SOCKET,RIGHT ANGLE,WITH FLANGE
				angles	linear: X.±0.5 / X.X±0.3 / X.XX±0.1	MM	
				X°±1°		scale	
				dr	EVIN ZHONG 050814		dwg no: KUxxC1x100J0G — sheet 1 of 1 — size A4
				engr	EVIN ZHONG 050814		
				chr	HANKE FENG 050814		type: CUSTOMER Drawing
				appd	SHI JUN 050814		
sheet index	revision	A					
	sheet	1					

Downloaded from Arrow.com.