All orders placed will be shipped out as usual, delivery times are expected to be affected due to COVID-19.Thank you for your continued support. Read More

Register to Get $10 Shipping Coupon

DFROBOT DRIVE THE FUTURE


Search

0

LOGIN/SIGN UP

HOME COMMUNITY NEW FORUM WIKI BLOG PRODUCT LINES EDUCATION $USD WISH LIST

Modules / LCDs/LEDs/E-ink/Displays / LEDs / Gravity: Flexible 8x32 RGB LED Matrix



Gravity: Flexible 8x32 RGB LED Matrix

SKU:DFR0462 Brand:Other Reward Points: 790

* Model: 8x8 | 8x32 | 16x16

Quantity: - +

ADD TO CART

Frequently Bought Together

Gravity: Flexible 8x32 RGB LED Matrix

Gravity: IO Exp... V7.1

You have choosen:0
Total amount:

BUY IT NOW

INTRODUCTION

Good news! There is a new member in to the Gravity family - The Flexible 8x32 RGB LED Matrix! This module is a square panel with a soldered XH2.54 3-pin interface with pin mappings that perfectly match the Arduino I/O expansion shield.

This flexible 8x32 RGB full-color LED matrix module is based on WS2812 or SK6812 intelligent control LEDs. Each LED can be independently addressed with RGB pixels that can achieve 256 levels of brightness. That's 16777216 colors in total with a scanning frequency no less than 400Hz!

The LED panel is single wire control board. We have customized a special cable to make it compatible with Arduino I/O expansion shields without any soldering. The module also supports cascading control. All you need to do is connect Din to the DOUT port. In combination with the open source Arduino library, you can control an entire array of LEDs using just one pin!

Note:
Each LED requires a maximum current of 18mA. When multiple modules are in use, it is recommended to use the DFRobot Gravity IO expansion board to power multiple LEDs matrix via the Servo Power Port.

FEATURES

- Full Color RGB
- Supports Cascade Control
- Compatible with Gravity Interface
- Supports External Power Supply

SPECIFICATION

Downloaded from Arrow.com.

- Operating Voltage: 5V
- LED Type: SK6812/WS2812
- Communication Interface: Gravity 3Pin interface
- Operating Temperature: -25 ~ +80 ℃
- Dimension: 80*320 mm/3.15*12.60 inches
- Weight: 188g

DOCUMENTS

- Product Wiki
- SK6812 Datasheet

SHIPPING LIST

- Flexible 8x32 RGB LED Matrix x1
- Matrix Gravity Interface Cable x1
- DC Barrel Jack Adapter - Female x1

REVIEW

FAQ

0 Comments DFRobot Disqus' Privacy Policy Login
Recommend Tweet Share Sort by Best
ırt the discussion...
Be the first to comment.
Subscribe Add Disqus to your site Do Not Sell My Data DISQUS

Sign up for exclusive offers!
Your email address
Like us on

Downloaded from Arrow.com.