



Through Hole Lamp Product Data Sheet

LTL-1BEDJ-012

Spec No.: DS20-2000-068

Effective Date: 07/29/2000

Revision: -

LITE-ON DCC


RELEASE

BNS-OD-FC001/A4

LITE-ON Technology Corp. / Optoelectronics
No.90,Chien 1 Road, Chung Ho, New Taipei City 23585, Taiwan, R.O.C.
Tel: 886-2-2222-6181 Fax: 886-2-2221-1948 / 886-2-2221-0660
<http://www.liteon.com/opto>

Features

- * Yellow and Green chips are matched for uniform light output.
- * Long life solid state reliability.
- * Low power consumption.
- * I.C. compatible.

Package Dimensions

Part No.	Lens	Source Color
LTL-1BEDJ-012	White Diffused	Yellow / Green

Notes:

1. All dimensions are in millimeters (inches).
2. Tolerance is $\pm 0.25\text{mm} (.010")$ unless otherwise noted.
3. Protruded resin under flange is 1.0mm (.04") max.
4. Lead spacing is measured where the leads emerge from the package.
5. Specifications are subject to change without notice.

Absolute Maximum Ratings at TA=25°C

Parameter	Yellow	Green	Unit
Power Dissipation	60	100	mW
Peak Forward Current (1/10 Duty Cycle, 0.1ms Pulse Width)	80	120	mA
Continuous Forward Current	20	30	mA
Derating Linear From 50°C	0.25	0.4	mA/°C
Reverse Voltage	5	5	V
Operating Temperature Range	-55°C to + 100°C		
Storage Temperature Range	-55°C to + 100°C		
Lead Soldering Temperature [1.6mm(.063") From Body]	260°C for 5 Seconds		



LITE-ON ELECTRONICS, INC.

Property of Lite-On Only

Electrical / Optical Characteristics at $T_A=25^\circ C$

Parameter	Symbol	Color	Min.	Typ.	Max.	Unit	Test Condition
Luminous Intensity	I_V	Yellow Green	5.7 5.7	19 19		mcd	$I_F = 20mA$ $I_F = 20mA$ Note 1,4
Viewing Angle	$2\theta_{1/2}$	Yellow Green		75 75		deg	Note 2 (Fig.6)
Peak Emission Wavelength	λ_p	Yellow Green		585 565		nm	Measurement @Peak (Fig.1)
Dominant Wavelength	λ_d	Yellow Green		588 569		nm	Note 3
Spectral Line Half-Width	$\Delta\lambda$	Yellow Green		35 30		nm	
Forward Voltage	V_F	Yellow Green		2.1 2.1	2.6 2.6	V	$I_F = 20mA$ $I_F = 20mA$
Reverse Current	I_R	Yellow Green			100	μA	$V_R = 5V$
Capacitance	C	Yellow Green		15 35		pF	$V_F = 0$, $f = 1MHz$

Note: 1. Luminous intensity is measured with a light sensor and filter combination that approximates the CIE (Commission International De L'Eclairage) eye-response curve.

2. $\theta_{1/2}$ is the off-axis angle at which the luminous intensity is half the axial luminous intensity.

3. The dominant wavelength, λ_d is derived from the CIE chromaticity diagram and represents the single wavelength which defines the color of the device.

4. The I_V guarantee should be added $\pm 15\%$.

Typical Electrical / Optical Characteristics Curves

(25°C Ambient Temperature Unless Otherwise Noted)




Fig.1 Relative Intensity vs. Wavelength




Fig.2 Forward Current vs. Forward Voltage




Fig.3 Forward Current Derating Curve




Fig.4 Relative Luminous Intensity vs. Forward Current




Fig.5 Luminous Intensity vs. Ambient Temperature





Fig.6 Spatial Distribution

Features

- * Compatible with radial lead automatic insertion equipment.
- * Most radial lead plastic lead lamps available packaged in tape and reel.
- * 3 leads with 2.54mm (0.1") straight lead spacing available.
- * Reel packaging simplifies handling and testing.

Package Dimensions

Item	Symbol	Specification			
		Minimum		Maximum	
		mm	inch	mm	inch
Tape Feed Hole Diameter	D	3.8	0.149	4.2	0.165
Component Lead Pitch	F	4.8	0.188	5.8	0.228
Front to Rear Deflection	△H	--	--	2.0	0.078
Feed Hole to Bottom of Component	H1	21.5	0.846	22.5	0.886
Feed Hole to Overall Component Height	H2	26.3	1.035	27.8	1.094
Lead Length after Component Height	L	W0		11.0	0.433
Feed Hole Pitch	P	12.4	0.488	13.0	0.511
Lead Location	P1	3.15	0.124	4.55	0.179
Center of Component Location	P2	5.05	0.198	7.65	0.301
Total Taped Thickness	T	--	--	0.90	0.035
Feed Hole Location	W0	8.5	0.334	9.75	0.384
Adhesive Tape Width	W1	12.5	0.492	13.5	0.531
Adhesive Tape Position	W2	0	0	3.0	0.118
Tape Width	W3	17.5	0.689	19.0	0.748