

GNSS - Automotive Grade Active External Puck Antenna



AECW0401G4Z

Request Samples



Check Inventory



Ø46.6 x 16.3 mm

RoHS/RoHS II Compliant

MSL Level = 1

Features

- Automotive Grade Antenna
- Manufactured in Automotive Certified lines
 - IATF 16949 certified
 - ISO 9001 certified
- Level-3 PPAP available upon request
- GNSS/GPS/GLONASS/BeiDou/QZSS
- IP67 rated
- RHCP
- High LNA gain of 28 dB
- Easy installation using screw

Applications

- IoT
- M2M
- Automotive Applications
- Geolocation Tracking
- Vehicle Tracking and Fleet Management
- Smart City
- Transportation
- Smart Agriculture

Product Image



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 05-12-20

ABRACON IS
ISO9001-2015
CERTIFIED

GNSS - Automotive Grade Active External Puck Antenna



AECW0401G4Z

Request Samples



Check Inventory



Ø46.6 x 16.3 mm

RoHS/RoHS II Compliant

MSL Level = 1

Part Number Builder

AECW0401G4Z -

Color / UV Coating	
Code	Description
S (Standard)	Black without UV coating
A	Black with UV Coating
B	White without UV Coating
C	White with UV Coating

Cable length in 'mm'	
Code	Description
3000 (Standard)	3000 mm
Other Examples :	
0200	200 mm
2000	2000 mm

Cable Type & Connector Type		
Code	Cable Type	Connector Type
S (Standard)	RG-174	SMA (M)
A		FAKRA C (F)
B		RP-SMA (M)
C		SMB (M)
D		N-Type (M)
E		TNC (M)
F		BNC (M)
G		MCX (M)
H		MMCX (M)
I		FME (M)
J		FME (F)
K		SMA (M)
L		FAKRA C (F)
M	LMR-100	RP-SMA (M)
N		SMB (M)
O		N-Type (M)
P		TNC (M)
Q		BNC (M)
R		MCX (M)
T		MMCX (M)
U		FME (M)
V		FME (F)

Example Configurations :

Part Number	UV Protection Coating / Color	Cable length	Cable Type / Connector Type
AECW0401G4Z S - <u>3000</u> S	No / Black	3000 mm	RG-174 with SMA (M) (Standard)
AECW0401G4Z A - <u>1000</u> A	Yes / Black	1000 mm	RG-174 with FAKRA C (M)
AECW0401G4Z B - <u>5000</u> O	No / White	5000 mm	LMR-100 with N-Type (M)

Note :

- For the standard part number (AECW0401G4Z), please refer to the packaging at the end of the document.
- For custom configurations (AECW0401G4Z -), MOQs, pricing and packaging changes may be applicable.



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 05-12-20

ABRACON IS
ISO9001-2015
CERTIFIED

GNSS - Automotive Grade Active External Puck Antenna



AECW0401G4Z

Request Samples



Check Inventory



Ø46.6 x 16.3 mm
RoHS/RoHS II Compliant
MSL Level = 1

Electrical Specification

Parameter		Specification			Unit
		Min	Typ	Max	
Center Frequency		1561		1602	MHz
VSWR				1.5	
Gain (Zenith)				2.0	dBic
Axial Ratio				3.0	dB
Impedance		50			Ω
Polarization		RHCP			
LNA					
Gain		26	28	30	dB
Noise Figure				1.5	dB
VSWR				2.0	
Ex-band Attenuation	@CF + 50 MHz		12		dB
	@CF – 50 MHz		16		dB
Supply Voltage (DC)		2.2		5	V
Current Consumption		5		15	mA
FILTER					
Insertion Loss				3.0	dB

Mechanical Specification

Parameter	Specification
Antenna Dimension	Ø46.6 x 16.3 mm
Radome Material	ABS
Mounting Type	Screw
RF Connector	SMA (M)
RF Cable	RG-174
Cable Length	3 m



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 05-12-20

ABRACON IS
ISO9001-2015
CERTIFIED

GNSS - Automotive Grade Active External Puck Antenna



AECW0401G4Z

Request Samples



Check Inventory




Ø46.6 x 16.3 mm
RoHS/RoHS II Compliant
MSL Level = 1

Environmental Specification

Parameter	Specification
Operating Temperature	-40°C to +85°C
Storage Temperature	-40°C to +85°C
Relative Humidity	Up to 95%
RoHS Compliance	Yes
PB Free	Yes
MSL	1
ESD Sensitive	Yes
Vibration	10 ~ 55 Hz with 1.5 mm amplitude 2 hrs
UL rating	UL-HB
Ingress Protection	IP67 (excluding cable outlet)

Product Dimension



Unit: mm



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 05-12-20

ABRACON IS
ISO9001-2015
CERTIFIED

GNSS - Automotive Grade Active External Puck Antenna



AECW0401G4Z

Request Samples




Check Inventory



Ø46.6 x 16.3 mm
RoHS/RoHS II Compliant
MSL Level = 1

Test Measurement - VSWR



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 05-12-20

ABRACON IS
ISO9001-2015
CERTIFIED

GNSS - Automotive Grade Active External Puck Antenna



AECW0401G4Z

Request Samples



Check Inventory



Ø46.6 x 16.3 mm


RoHS/RoHS II Compliant

MSL Level = 1


Radiation Characteristics

2D Pattern


XY - Plane



XZ - Plane



YZ - Plane



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 05-12-20

ABRACON IS
ISO9001-2015
CERTIFIED

GNSS - Automotive Grade Active External Puck Antenna



AECW0401G4Z

Request Samples



Check Inventory



Ø46.6 x 16.3 mm
RoHS/RoHS II Compliant
MSL Level = 1

Packaging Information

Number of Antenna/ Carton : 100 pcs
Weight of 1 pc of the antenna : 100 g
Dimension of the Carton : 490 x 230 x 270 mm
Weight of the Carton : 11 kg

ATTENTION: Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 05-12-20

ABRACON IS
ISO9001-2015
CERTIFIED