






REV.	DATE	DESCRIPTION
NC	10/04/07	INITIAL RELEASE



NOTE:

1. CRIMPED FERRULE HEX CRIMP SIZE .128"
2. CONTACT PIN TO SOLDER.

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex									
8						DRAWN	G.R.S.	10/04/07											
7						CHECKED													
6	HEAT SHRINK TUBE			1							PART DESCRIPTION SMC R/A CRIMP PLUG (RG-174/U, 188A/U, 316/U)								
5	FERRULE	COPPER	GOLD	1															
4	COVER	BRASS	GOLD	1															
3	CONTACT PIN	BER. COPPER	GOLD	1								PART NO. 152107							
2	INSULATOR	TEFLON	NATURAL	1															
1	BODY	BRASS	GOLD	1															
	DESCRIPTION	MATERIAL	FINISH	QTY			CAD FILE		C:/152/152107.DWG		DWG. NO.	152107.DWG		REV.	NC	SIZE	A	SCALE	NA