




Pro/E

3

cage code 22526

4



PRODUCT NUMBER	DIM	LENGTH FORMULAS (SEE NOTE 9)
51707-ABB00000EF__ NOTE: 3	DIM "A"	.250 [6.35] x BB + .090 [2.29] (NOTE 9)
SEE NOTE 1	DIM "F"	.250 [6.35] x BB + .120 [3.05]

CONNECTOR NOTES:

- ①. PRODUCT NUMBER CODE:
51707 - A BB 000 00 E F LF
- NO THIS SUFFIX: 100u"/2.54um SnPb ON PCB INTERACE
ADD THIS SUFFIX: 78u"/2.00um Sn OR 5u" Au ON PCB INTERFACE
ALWAYS "0" (ZERO) (NOTE 7)
TAIL OPTIONS (NOTE 6)
ALWAYS '00' (ZERO,ZERO)
ALWAYS '000' (ZERO,ZERO,ZERO) (NOTE 5)
NUMBER OF POWER CONTACTS (NOTE 4)
PLATING (NOTE 3)
BASE NUMBER

- ②. HOUSING MATERIAL: UL94 V-0 HIGH GLASS FILLED TEMP THERMO PLASTIC
POWER CONTACT MATERIAL: COPPER ALLOY
- ③. 51707-1BB00000EF;51707-1BB00000EFLF;51707-3BB00000EFLF PLATING SPEC.
SEE PRINT:10064183

- ④. POWER CONTACTS, 01 TO 20 AVAILABLE.
MAXIMUM OF 20 POWER CONTACTS PER CONNECTOR

- ⑤. THIS PART IS NOT AVAILABLE WITH SIGNAL CONTACTS.

- ⑥. TAIL OPTIONS:
A = 0.135 +0.015/-0.010 [3.43 +0.38/-0.25] SOLDER TO BOARD
B = 0.165 +0.015/-0.010 [4.19 +0.38/-0.25] SOLDER TO BOARD
C = 0.165 +0.015/-0.010 [4.19 +0.38/-0.25] PRESS FIT

- ⑦. BOARD RETENTION NOT AVAILABLE WITH GUIDELESS ENDS.

- ⑧. MANUFACTURE'S NAME, P/N, AND DATE CODE
TO APPEAR ON THIS SURFACE.

- ⑨. THE MAXIMUM OVERALL LENGTH (DIM A) OF A PART
IS 8.00 [203.2]

10. PRODUCT SPECIFICATION GS-12-149

11. SEE PWRBLADE VERTICAL HEADER SPECIAL
WORKSHEET (51696) FOR MATING LENGTH OPTIONS.

12. DIMENSIONS AND TOLERANCES ARE IN ACCORDANCE
WITH ASME Y14.5M, 1994 UNLESS OTHERWISE

PCB NOTES:

13. ALL DIMENSIONS ARE BASIC UNLESS OTHERWISE SPECIFIED.

14. ALL THROUGH HOLES ARE LOCATED WITH A
TRUE POSITION OF 0.004 [0.10]

15. ALL HOLE DIAMETERS ARE FINISHED HOLE SIZE.

16. $\varnothing 0.0453 \pm 0.0010$ [1.151 ± 0.025] DRILLED HOLES PLATED WITH
0.0003 [0.008] MIN SnPb OVER 0.001 [0.03] TO 0.003 [0.08] Cu
PLATING TO ACHIEVE A $\varnothing 0.040 \pm 0.003$ [1.02 ± 0.07] HOLE.

17. FOR PRESS FIT APPLICATION USE FCI CAM
TOOL 430169-XXX.

mat'l code SEE NOTE 2				tolerances unless otherwise specified		CUSTOMER		FCI	
ltr	ecn no.	dr	date	linear	.XX±.01/.X±0.3	COPY		www.fciconnect.com	
E					.XXX±.005/.XX±0.13	projection		title	
				angles	.XXX±.0020/.XXX±.051			VERTICAL HEADER w/o GUIDE PIN POWER	
				dr	0°±2°			product family	
				enrg	JRW 10-16-01	INCH/MM		PWRBLADE	
				chr	J. ALLISON 10-16-01	scale		code	
				appd	J. ALLISON 10-16-01	3:2		213	
sheet index	revision sheet							size	sheet
								A	2

cage code 22526

Pro/E

3

4

