




CONNECTOR PIN OUT	
PIN NO.	DIAGRAM NO.
1 (G33D20)	1 (COM)
2 (G15F20)	2 (COM)
3 (G17C20)	3 (NO)
4 (G6C20)	4 (NO)

[illegible]

- NOTES
- 1 - CORROSION RESISTANT STEEL : EXTERNAL METALS
 - 2 - SWITCH SEALED PER MIL-S-8805, SYMBOL 3
 - 3 - CIRCUIT DIAGRAM, CATALOG LISTING, DATE CODE, FED. MFG. CODE, AND CUSTOMER SCD # 002-384003-1 ARE SHOWN ON NAMEPLATES
 - 4 4X #20 AWG WIRE LEAD PER MIL-W-22759/7
MARKED WITH CIRCUIT IDENTIFICATION AND WIRE GAGE
(1-20, 2-20, ETC) PER MIL-W-5088
 - 5 CONNECTOR AMP 206153-1, CLAMP AMP 206062-1, OR EQUIVALENT
PIN AMP 66103-2 (QTY.4)
 - 6 PROTECTIVE OVERSLEEVING PER BENTLEY HARRIS
TYPE H MATERIAL

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH. A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH			THIRD ANGLE PROJECTION 	
CHARACTERISTICS		ELECTRICAL DATA		
OPERATING FORCE — — — 3-6 LBS FULL OVERTRAVEL FORCE— — — 17 LBS MAX RELEASE FORCE — — — 2 LBS MIN PRETRAVEL — — — .040 MAX DIFFERENTIAL TRAVEL — — — .020 MAX OVERTRAVEL — — — .250 MIN		CONTACT ARRANGEMENT 2X S.P.N.O.		
		DO NOT SCALE PRINT		
		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE		
		ONE PLACE (.) ±.030		
		TWO PLACE (.00) ±.015		
		THREE PLACE (.000) ±.005		
		ANGLES ±		
		WEIGHT		

ANSI Y14.5M-1982 APPLIES