






PRODUCT NUMBER

SEE SHEET 2



spec ref *				dr	Rainbow Zhan	2016/12/14	projection	MM	size	A3	scale	3:2						
tolerance std				eng	Rainbow Zhan	2018/05/08			ecn no				ELX-DG-30121-1					
ISO 406				chr	-	-			rel level				Released					
ISO 1101				appr	Zheng, Pei-Min	2018/05/10			product family				PwrBlade+					
surface ISO 1302	linear	0.X	±0.5	Amphenol FCI 68S RA STB PLUG				dwg no	10106262-0017101				rev	B				
		0.XX	±0.25															
		0.XXX	±0.10															
	angular	0°	±2°	www.fci.com				cat. no.				Product - Customer Drw				sheet 1 of 3		

PRODUCT NO.	ROWS	SIGNAL																	E2				
		E1	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16		17			
10106262-0017101LF	D C B A		U	U	U	U	U	U	U	U	U	U	U	U	U	U	X	U	U				
			T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	X	T		T		
			S	S	S	S	S	S	S	S	S	S	S	S	S	S	S	X	S		S		
			R	L	R	R	R	R	R	R	R	R	R	R	R	R	R	L	X		R	R	
			H	A																		H	A
				U	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U				




CODE	DESCRIPTION
HA	HOLD DOWN WITH PLATED
R	STD SIGNAL CONTACT, ROW A (3.43)
RL	MFBL SIGNAL CONTACT, ROW A (3.43)
S	STD SIGNAL CONTACT, ROW B (3.43)
T	STD SIGNAL CONTACT, ROW C (3.43)
TL	MFBL SIGNAL CONTACT, ROW C (3.43)
U	STD SIGNAL CONTACT, ROW D (3.43)
UL	MFBL SIGNAL CONTACT, ROW D (3.43)
X	OMITTED

spec ref	*	dr	Rainbow Zhan	2016/12/14	projection	MM	size	A3	scale	3:2
tolerance std	ISO 406 ISO 1101	eng	Rainbow Zhan	2018/05/08	chr	-	ecn no	ELX-DG-30121-1	rel level	Released
surface	linear	appr	Zheng, Pei-Min	2018/05/10	product family	PwrBlade+	cat. no.	68S	dwg no	10106262-0017101
ISO 1302	angular								rev	B

NOTES:

- 1) PRODUCT MARK:
PART NUMBER AND DATE CODE TO BE MARKED ON THIS SURFACE .
THE MARK CAN BE OMITTED IF THERE IS NOT ENOUGH SPACE ON THIS SURFACE.
- 2) MATERIALS:
-HOUSING : HIGH TEMP THERMOPLASTIC WITH GLASS FIBER, UL94V-0, BLACK.
-POWER CONTACT : HIGH CONDUCTIVITY COPPER ALLOY.
-SIGNAL CONTACT : COPPER ALLOY.
- 3) PLATING SPECIFICATION : 10124315
- 4) DENOTES CONNECTOR KEEP OUT ZONE.
- 5) DATUM AND BASIC DIMENIONS ARE ESTABLISHED BY CUSTOMER.
- 6) ALL HOLE DIAMETERS ARE FINISHED HOLE SIZES.
- 7) 1.15+/-0.025MM DRILLED HOLE PLATED WITH 0.00762MM MIN SN
OVER 0.0254-0.0762MM CU PLATING TO ACHIEVE A 1.02+/-0.07MM HOLE.
- 8) THE HOUSING WILL WITHSTAND EXPOSURE TO 265 °C PEAK TEMPERATURE
FOR 10 SECONDS IN A WAVE SOLDER APPLICATION.
- 9) THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY
REGULATIONS AS DESCRIBED IN GS-47-0004.
- 10)PRODUCT SPECIFICATION : GS-12-658.
APPLICATION SPECIFICATION : GS-20-141.
PRODUCT PACKAGE SPECIFICATION: GS-14-1502.

spec ref *				dr	Rainbow Zhan	2016/12/14	projection 	MM 	size	A3	scale	3:2
tolerance std ISO 406 ISO 1101	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Rainbow Zhan	2018/05/08			ecn no	ELX-DG-30121-1		
				chr	-	-			rel level Released			
				appr	Zheng, Pei-Min	2018/05/10	product family PwrBlade+					
surface  ISO 1302	linear	0.X	±0.5	Amphenol FCi	title 68S RA STB PLUG	dwg no 10106262-0017101	rev B					
		0.XX	±0.25									
		0.XXX	±0.10									
	angular	0°	±2°	www.fci.com	cat. no.	Product - Customer Drw		sheet 3 of 3				