

MLG0603S1N2CTD25

**Applications**

Automotive Grade

AEC-Q200

AEC-Q200

Feature

Multilayer

Multilayer

Non-Mag Core

Non-Magnetic Core (Dielectric Ceramic)

Series | Type

MLG

Status

Production

Brand

TDK

**Size**

Length(L)	0.60mm \pm 0.03mm
Width(W)	0.30mm \pm 0.03mm
Thickness Height	0.30mm \pm 0.03mm
Recommended Land Pattern (A)	0.25mm Nom.
Recommended Land Pattern (B)	0.30mm Nom.
Recommended Land Pattern (C)	0.30mm Nom.

Electrical Characteristics

Inductance	1.2nH \pm 0.2nH at 100MHz
Rated Current	550mA
DC Resistance [Typ.]	60m Ω
DC Resistance [Max.]	150m Ω
Self Resonant Frequency [Min.]	10GHz
Self Resonant Frequency [Typ.]	12.3GHz
Q [Min.]	4 at 100MHz
Q [Typ.]	

Other

Operating Temp. Range	-55 to 125°C
Soldering Method	Reflow Iron Soldering
AEC-Q200	YES
Packing	Punched (Paper)Taping [180mm Reel, Tape width 8mm]
Package Quantity	15000pcs
Weight	0.0002g

! Images are for reference only and show exemplary products.





! This PDF document was created based on the data listed on the TDK Corporation website.

! All specifications are subject to change without notice.

MLG0603S1N2CTD25



Characteristic Graphs (This is reference data, and does not guarantee the products characteristics.)





! Images are for reference only and show exemplary products.
! This PDF document was created based on the data listed on the TDK Corporation website.
! All specifications are subject to change without notice.

MLG0603S1N2CTD25



Associated Images



! Images are for reference only and show exemplary products.
! This PDF document was created based on the data listed on the TDK Corporation website.
! All specifications are subject to change without notice.