


PRODUCT NUMBER	PITCH
NMxx100100J0G	3.50mm

1





2

3

4



The color of lever is consistent with body's



N=Number of poles

Dim L=N×3.5+0.70

Dim P=(N-1)×3.5

Poles	Tolerance
2-6p	±0.15
7-12p	±0.20
13-18p	±0.30
19-24p	±0.40

PART NO.: NM xx 10 0 1 00J0 G

End stackable
No. of poles
02 2 poles
03 3 poles
...
24 24 poles

RoHS compliant
(lead<4%)
In copper Alloy

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family	TERMINAL BLOCK		
ltr	ecn no	dr	date	tolerances unless otherwise specified			scale	dwg no	sheet 1 of 1	size
				angles	dr	X.±0.5				
				dr	dr	X.X±0.3				
				dr	dr	X.XX±0.1				
				dr	EVIN ZHONG	060614				
				engr	EVIN ZHONG	060614				
				chr	HANKE FENG	060614				
				appd	SHI JUN	060614				
sheet	revision	A								
index	sheet	1								



PDS: Rev :A 3

STATUS:Released

Printed: Jul 18, 2014