





REVISION RECORD				
REV	ECN	DESCRIPTION	DRFT	DATE



仅供参考图

日期: 2016.07.11

NOTES1:

UL Standard

1. Rated voltage/current : 600V / 100A
2. Withstanding voltage : AC2200V/1Min.
3. Torque value : M5 , 27.0Lb.in
4. Wire range : 14~3AWG

IEC Standard

1. Pollution degree	3
Overvoltage category	III
Rate impulse voltage(KV)	8.0KV
Rate voltage(V)	1000V
Rate current(A)	76 A

2. Torque value : M5 , 2.5N·m
3. Wire range : 1.5~25mm²

NOTES2:

1. Dimension shall be interpreted per ASME Y14.5-2009
2. Pitch : 12mm, Poles : N=01P
3. Stripping length : 12~13mm
4. Operating temperature: -40°C~+105°C
5. Undimensioned tolerances:

Pitch range in mm		Nominal dimension range in mm						
TO	Over	TO	Over	TO	Over	TO	Over	
6	10	10	24	30	60	100	150	0.1/10
6	10	24	30	60	100	150		<
								±2'

6. RoHS Compliance

ITEM	NAME OF PART	MATERIAL	NOTES
4	Screw	STEEL	M5/Zn plated
3	Current carrier	COPPER	Sn plated
2	Cage	STEEL	M5/Zn plated
1	Housing	PA66	UL94V-0

DETACHED LISTS	PART NO.:	NINGBO DEGSON ELECTRICAL CO., LTD		
	APPD:	NAME: DC16-01P-1Y-00A(H)		
	CHKD:	DRAWING NO.: DC16-C01		
	DRFT:	REV D0-1		
THIRD ANGLE PROJECTION		DO NOT SCALE DRAWING	SCALE	1:1