



Part Number : [1200905074](#)
Product Description : Nano-Change (M8) Receptacle, M8 x 0.5 Mounting Threads, Male (Straight) to Leads, 0.20m (7.87") Length, with 4 Poles on Mating Side
Series Number : 120090
Status : Active
Product Category : Circular Industrial Connectors
Engineering Number : 4R4F06E02C200




Documents & Resources

Drawings
[1200905074_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead; Lead monoxide per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	120090
Description	Nano-Change (M8) Receptacle, M8 x 0.5 Mounting Threads, Male (Straight) to Leads, 0.20m (7.87") Length, with 4 Poles on Mating Side
IP Rating	IP67
NEMA Rating	NEMA 6
Product Name	Nano-Change (M8)
Type	Single Ended (pigtail)
UPC	883906784515

Agency

UL	E152210
----	---------

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V AC / 75V DC

Physical

Coupling Type	External Thread
Gender	Male
Keyway	None
Length	0.20m
Material - Component	Nickel-plated Brass
Mounting Thread Size	M8 x 0.5
Orientation	Straight
Panel Mount	Back, Front
Poles	4
Temperature Range - Operating	-25° to +90°C

Wire/Cable Type	Leads
Wire Size (AWG)	24

This document was generated on Apr 26, 2025