



Part Number : [1462340200](#)
Product Description : 698MHz-6GHz Wide Band Antenna, 200.00mm Cable Length, Compatible with U.FL / I-PEX MHF Connectors
Series Number : 146234
Status : Obsolete
Product Category : Antennas



Documents & Resources

Specifications

[1462340100-AS.pdf](#)
[1462340100-PS.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Antennas
Series	146234
Description	698MHz-6GHz Wide Band Antenna, 200.00mm Cable Length, Compatible with U.FL / I-PEX MHF Connectors
Component Type	Flexible Antenna with Cable
Function	Signal
Product Name	698MHz-6GHz Wide Band Antenna
Protocol	Cellular
Type	Cellular Antenna
UPC	191128461689

Electrical

Band#1 F_End (MHz)	960
Band#1 F_Start (MHz)	698
Band#2 F_End (MHz)	2700
Band#2 F_Start (MHz)	1500
Band#3 F_End (MHz)	6000
Band#3 F_Start (MHz)	2700
Electrical Connectivity	Cable
Peak Gain (dBi)	1.6 @ 698 MHz, 2.5 @ 1500 MHz, 4.6 @ 2.7 GHz
Return Loss - S11 (dB)	< -4, < -5
Total Efficiency	>64% @ 2.7 GHz, >66% @ 1500 MHz, >68% @ 698 MHz

Physical

Cable Length	200.00mm
--------------	----------

Length	140.00mm
Mounting Style	Adhesive
Net Weight	1.580/g
Packaging Type	PET Film
Polarization	Linear
Radiation Pattern	Omnidirectional
Thickness	0.10mm
Width	20.00mm

Mates With / Use With

Mates with Part(s)

Description	Part Number
MCRF Jack, Straight, PCB Receptacle, Surface Mount, 1.25mm Mounted Height, 50 Ohms	<u>734120110</u>

This document was generated on Sep 17, 2025