


DIMENSIONS




TIN LEAD PART NUMBER

PART NUMBER
86093947113H40264E1

LEAD FREE PART NUMBER

PART NUMBER
86093947113H40AOLF

TERMINATION




SPECIFICATION 264 = no contact in position : C15-C31
or SPECIFICATION AO=


GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C-8609-0000A

P.C. CARD DRILLING (Component side view)

See drawing ref. C-8609-0000



rev	ecn no	dr	date
A	-	-	2001/01/31
B	LS05-001	JTA	2005/03/03
C	LS06-0095	LGO	2006/06/26
D	ELX-I-41744	MJA	2021/07/21
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 			
			TOLERANCES UNLESS OTHERWISE SPECIFIED									
Dr	ROUILLARD	2001/01/31	ANGULAR		LINEAR		0.X		±0.1		size A3	Scale 1.5
Eng	TARON	2001/01/31					0.XX		±0.1			
Chr	M JACOB	2021/07/21	0.XX' ±2				0.XXX		±0.1		ECN ELX-I-41744	
Appr	SANOJ	2021/07/21	Product family DIN 8609						Spec ref -			
Amphenol FCI		title STANDARD MALE 3 ROW 94 CONTACTS					dwg no C-8609-0880					Rev. D
		catalog no					CUSTOMER					sheet 1 of 1