




+ CONNECTORS

SFP/SFP+/ZSFP+



✓ Active

TE CONNECTIVITY (TE)
zSFP+ STACKED 2X1 RECEPTACLE ASSEMBLY

[zSFP+/SFP28](#) | [zSFP+](#)

2-2198318-0
TE Internal Number: 2-2198318-0

[Not Yet Reviewed for EU RoHS](#)
[Not Yet Reviewed for EU ELV](#)

Form Factor zSFP+
Product Type Cage Assembly with Integrated Connector
Data Rate (Max) (Gb/s) 32
EMI Containment External Springs
Cage Type Stacked

[↓](#) **PRODUCT DRAWING**
English

[↓](#) **3D PDF**

DOCUMENTATION

Product Drawings
RECEPTACLE ASSEMBLY, 2X1, STACKED, ZSFP+
PDF
English

CAD Files
3D PDF
PDF
3D

Customer View Model
2D_DXF.ZIP
English
Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Catalog Pages/Data Sheets

1-1773707-6 ZSFP+ Interconnect Brochure

PDF

English

Product Specifications

Product Specification

ZSFP+ Stacked Connector And Cage Assemblies

PDF

English

Application Specification

Stacked Small Form-Factor Pluggable ZSFP+ Connector And Cage Assembly

PDF

English

Instruction Sheets

Instruction Sheet (U.S.)

Small Form-Factor Pluggable (SFP)+ ZSFP+ Extraction Tool Kits 2063048-[] And 2161405-1 For Stacked PT Connector And Cage Assemblies

PDF

English

Small Form-Factor Pluggable (ZSFP+) Seating Tool Kits 2215000-[] For Stacked PT Connector And Cage Assemblies

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

- Form Factor zSFP+
- Product Type Cage Assembly with Integrated Connector
- Included Heat Sink No
- Included Lightpipe Yes
- Integrated Lightpipes Yes

Configuration Features

EMI Containment External Springs
Port Configuration 2 x 1
Lightpipe Configuration Reversed Outer
Lightpipe Style Standard
Number of Ports 2

Signal Characteristics
Data Rate (Max) (Gb/s) 32

Contact Features
Tail Plating Material Tin
Contact Mating Area Plating Material Gold or Gold Flash over Palladium Nickel
Contact Mating Area Plating Thickness .76 µm [29.92 µin]

Termination Features
Termination Method to PC Board Through Hole - Press-Fit

Mechanical Attachment
PCB Mounting Style Single-Sided

Housing Features
Cage Type Stacked
Cage Material Nickel Silver Alloy

Dimensions
Tail Length 1.8 mm [.07 in]
PCB Thickness (Recommended) 1.5 mm [.059 in]

Operation/Application
For Use With zSFP+ SMT Connector
Heat Sink Compatible No

Industry Standards
UL Flammability Rating UL 94V-0

Packaging Features
Packaging Method Tray

Statement of Compliance
Statement of Compliance
PDF