


OGA DIAGONAL: 13.18 [334.68]
VA DIAGONAL: 12.57 [319.28]
PA DIAGONAL: 11.89 [302.13]

TOP LEVEL NUMBER	SKU NUMBER	TYPE	DIM "A" (TOTAL GLASS TO CONNECTOR)	A/G FINISH	PRODUCT SPEC
87-4011-201	98-0003-2748-0	NOV	SEE DWG	AG500	33264



- NOTES:
1. WEIGHT OF GLASS IN GRAMS: 961 ± 10%.
 2. DIMENSIONS AND TOLERANCES DO NOT APPLY TO AREA 15 MM AROUND HARNESS EXIT.

UNITS	INCHES [MM]
TOLERANCES UNLESS OTHERWISE SPECIFIED	
.X	± .03 [.76]
.XX	± .015 [.38]
.XXX	± .01
ANGLES	± 1°
THIRD ANGLE PROJECTION	
DO NOT SCALE DRAWING	
SCALE	1 = 1

3M 3M TOUCH SYSTEMS
METHUEN, MA
USA
© COPYRIGHT 2007
THIS DOCUMENT IS COPYRIGHTED PROPERTY OF THE
3M COMPANY AND MAY NOT BE REPRODUCED
WITHOUT 3M WRITTEN PERMISSION OR USED OR
DISCLOSED FOR OTHER THAN 3M AUTHORIZED
PURPOSES.

03	REVISED PER CO 030448	5/09	SEB
02	REVISED PER CO 029071	6/08	SEB
01	INITIAL RELEASE PER CO 027007	3/07	MTD
REV	CHANGE NOTICE	DATE	DRW
TITLE			
MARKETING DRAWING SCT76NN 12.57"			
DRWN	MTD	3/8/07	GAD FORMAT AUTOCAD
SHEET	1 OF 1	DOC NO.	33597-MKT
REV	03		