



**Part Number :** [22052031](#)

**Product Description :** KK 254 Wire-to-Board Header, Single Row, Right-Angle, 3 Circuits, PA Polyamide Nylon, Tin (Sn) Plating

**Series Number :** 4094

**Status :** Active

**Product Category :** PCB Headers and Receptacles

**Engineering Part Number :** A-4094-03A197



---

## Documents and Resources

### Drawings

[022052031\\_sd.pdf](#)

[PK-4094-001-001.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

[SYM-22-05-2031-001.zip](#)


### Specifications

[PS-10-07-001.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |   |
|--------------------|---|
| GADSL/IMDS         | Compliant with Exemption 44; 33   |
| China RoHS         |  per SJ/T 11365-2006 |
| EU ELV             | Not Relevant  |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21  |
| REACH SVHC         | Not Contained per D(2025)7771-DC (04 Feb 2026)  |
| EU RoHS            | Compliant per EU 2015/863   |

## Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

## Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

## Part Details

### General

|                |  |
|----------------|--|
| Status         | Active   |
| Category       | PCB Headers and Receptacles  |
| Series         | 4094   |
| Description    | KK 254 Wire-to-Board Header, Single Row, Right-Angle, 3 Circuits, PA Polyamide Nylon, Tin (Sn) Plating |
| Application    | Board-to-Board, Wire-to-Board  |
| Component Type | PCB Header   |
| Product Name   | KK 254   |
| UPC            | 800753739680   |

### Agency

|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

### Electrical

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 4.0A |
| Voltage - Maximum             | 500V |

### Physical

|                                |                           |
|--------------------------------|---------------------------|
| Breakaway                      | No                        |
| Circuits (Loaded)              | 3                         |
| Circuits (maximum)             | 3                         |
| Color - Resin                  | Natural (White)           |
| Durability (mating cycles max) | 25                        |
| First Mate / Last Break        | No                        |
| Flammability                   | 94V-0                     |
| Glow-Wire Capable              | No                        |
| Lock to Mating Part            | No                        |
| Material - Metal               | Brass                     |
| Material - Plating Mating      | Tin                       |
| Material - Resin               | Nylon                     |
| Net Weight                     | 0.242/g                   |
| Number of Rows                 | 1                         |
| Orientation                    | Right Angle               |
| Packaging Type                 | Bag                       |
| PCB Locator                    | No                        |
| PCB Retention                  | No                        |
| PCB Thickness - Recommended    | 1.60mm                    |
| PC Tail Length                 | 3.15mm                    |
| Pitch - Mating Interface       | 2.54mm                    |
| Pitch - Termination Interface  | 2.54mm                    |
| Polarized to Mating Part       | No                        |
| Polarized to PCB               | No                        |
| Shrouded                       | Unshrouded                |
| Stackable                      | Yes                       |
| Temperature Range - Operating  | See Product Specification |
| Termination Interface Style    | Through Hole              |

### Solder Process Data

|                              |      |
|------------------------------|------|
| Max-Duration                 | 5    |
| Lead-Free Process Capability | WAVE |
| Max-Cycle                    | 1    |
| Max-Temp                     | 235  |

## Mates With / Use With

### Mates with Part(s)

| Description                      | Part Number |
|----------------------------------|-------------|
| KK 254 Single Row Crimp Housings | <u>2695</u> |
| KK 254 PC Board Connector        | <u>4455</u> |
| KK 254 Receptacle Housings       | <u>7880</u> |

---

This document was generated on May 21, 2026