








P.C. LAYOUT



Tolerances: ≤6: ±0.2mm 6-18: ±0.4mm			Date	Name	TME 1	
			08/09	dr		
					30 19 05	
Modifications			Date	Name	knitter-switch	
					Page	
					1/2	

Specifications:

Contact rating:	50mA, 48V DC, max. 1W
Contact resistance:	100mOhm max.
Insulation resistance:	100MOhm min. at 100V DC
Dielectric strength:	250V, 50Hz for the duration of 1 minute
Operating temperature:	-25°C to +70°C
Mechanical life:	min. 300 000 cycles
Operating force:	2.0N
Soldering conditions:	auto-soldering: max.: 275 +/-10°C, 6sec.
Switching function:	off - mom
Mounting:	on pc-board
Material:	Terminals: PC terminals
	Contacts: phosphor bronze, silver plated
	Case: 6TPA resin, washable
	Frame: stainless steel
	Button: perbunan, black

CIRCUIT CHARACTERISTICS

Circuit arrangement		Diagram	Terminals
free off	push (on)		6
—	(1) (2) (3) (4)		



Tolerances: ≤6: ±0.2mm 6-18: ±0.4mm			Date	Name	TME 1		
			08/09	dr			
					30 19 05		
					knitter-switch		Page
							2/2
Modifications	Date	Name					