

Uninsulated Terminals and Splices (Continued)


**SOLISTRAND
High Temperature
Ring Tongue Terminals**

**Temperature Rating
and Material**

Terminal Body — Nickel per
ASTM B162, 1200°F [649°C]

Related Product Data

Application Tooling — pages 9022
and 9023



Non-Insulation Support

Wire Size Circular Mils [mm ²]	Tongue Material Thickness Max.	Color Code	Stud Size	Dimensions				Part Number Loose Piece
				W	C Min.	E Max.	L Max.	
12-10 5,180-13,100 [2.62-6.64]	.042 1.07	Orange	8 M4	.375 9.53	.281 7.14	.549 13.94	.739 18.77	323745*
			10	.375 9.53	.281 7.14	.549 13.94	.739 18.77	323680*
			1/4 M6	.531 13.49	.468 11.89	.736 18.69	1.004 25.50	323683*
8 13,100-20,800 [6.64-10.5]	.051 1.30	Orange	10	.406 10.31	.359 9.12	.743 18.87	.949 24.10	328822

*Available in small packaging quantities.


**SOLISTRAND
High Temperature
Splices**

**Temperature Rating
and Material**

Splice Body — Nickel per
ASTM B162, 1200°F [649°C]

Related Product Data


Application Tooling — pages 9022
and 9023



**Style-A
Non-Insulation
Support
Butt Splice**



**Style-B
Non-Insulation
Support
Parallel Splice**



**Style-C
Non-Insulation
Support
Butt Splice**

Wire Size Circular Mils [mm ²]	Material Thickness Max.	Color Code	Style	Dimensions			Part Number Loose Piece
				L Max.	ID Min.	OD Max.	
22-16 509-3,260 [0.26-1.65]	.033 0.84	Orange	A	.578 14.68	.061 1.55	.141 3.58	322324*
			B	.301 7.65	.061 1.55	.141 3.58	322326
16-14 2,050-5,180 [1.04-2.62]	.033 0.84	Orange	A	.567 14.40	.085 2.16	.165 4.19	322345
			B	.301 7.65	.085 2.16	.165 4.19	322347
			C	.529 13.44	.085 2.16	.165 4.19	323878
12-10 5,180-13,100 [2.62-6.64]	.042 1.07	Orange	A	.567 14.40	.129 3.28	.226 5.74	323696*
			B	.333 8.46	.129 3.28	.226 5.74	323672
			C	.703 17.86	.129 3.28	.226 5.74	323698

*Available in small packaging quantities.