





NOTES:

1. METAL SHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
2. INSULATORS: PBT GF UL 94 V-0, BLACK
3. CONTACTS: COPPER ALLOY
PLATING: 30µin HARD GOLD over min. 50µin NICKEL
4. METAL BRACKET: STEEL; min. 320µin TIN over 80µin NICKEL
5. THREADED INSERT: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
6. P.C.B. SNAP: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
PCB-HOLE: $\phi 3.1 \pm 0.1$; PCB THICKNESS 1.6mm
7. FIXING-PLATE: PBT GF UL 94 V-0; BLACK
8. PCB HOLE DRILLINGS ON SHEET 2
9. MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
10. CONNECTOR IS PART MARKED: 163C18569X CONEC ABC

Directive 2002/95/EC
"RoHS"
Compliant

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

6 x b	A	3013	09.05.08	Lehm.	tolerance	dim. in mm	scale:	material:	title:
a	Origin				date	name	2:1 (5:1)	SEE NOTES	D-SUB MALE 90°
rev.	description	date	name		drawn	21.08.07	Lehmenkühler		50pos. 0.318inch
					appd.	21.08.07	Mickenbecker		threaded insert, metal bracket, fixing-plate, snap
					norm				dwg no: Inventor 10
					d-old				DIN-A3
									sh: 1

CONEC

part no:	163C18569X
----------	------------

