
Part Number : 551000680
Product Description : 2.00mm Pitch Serial I/O Connector, Plug Kit, Wire-to-Wire, Solder Type, 6 Circuits, Tray
Series Number : 55100
Status : Active
Product Category : I/O Connectors



Documents and Resources

Drawings

551000680_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

551000680AS-A00.pdf

551009200-200.pdf

PS-54280-005-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains 2-(2H-Benzotriazol-2-yl)-4-(1,1,3,3-tetramethylbutyl)phenol; Perfluorobutane sulfonic acid (PFBS) and its salts per D(2025)7771-DC (04 Feb 2026)

Downloaded from Arrow.com.

EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	I/O Connectors
Series	55100
Description	2.00mm Pitch Serial I/O Connector, Plug Kit, Wire-to-Wire, Solder Type, 6 Circuits, Tray
Application	Wire-to-Wire
Component Type	Plug
Product Name	2.00mm I/O Connectors
Type	N/A
UPC	191128366199

Electrical

Current - Maximum per Contact	2.0A
Shielded	Yes
Voltage - Maximum	125V AC (RMS)/DC

Physical

Downloaded from Arrow.com.

Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Black, Gray
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze, Stainless Steel
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic, Polycarbonate
Net Weight	9414.493/mg
Orientation	Vertical
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	2.00mm
Plating min - Mating	0.762µm
Plating min - Termination	2.032µm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +85°C
Termination Interface Style	N/A
Wire Insulation Diameter	2.10mm max.
Wire Size (AWG)	16, 18, 20, 22, 24, 26, 28

Mates With / Use With

Mates with Part(s)

Description	Part Number
2.00mm Pitch IEEE 1394-1995 Shielded I/O PCB Socket, Right-Angle, Flat, Surface Mount, 6 Circuits, Tray Packaging	534620629
2.00mm Pitch Serial I/O Connector, Socket Kit, Wire-to-Wire Crimp Type, Without Flange, 6 Circuits	5006550609
2.00mm Pitch Serial I/O Connector, Socket Kit, Wire-to-Wire Crimp Type, With Flange, 6	5006550619

Downloaded from Arrow.com.

Circuits	
2.00mm Pitch Serial I/O Connector, Receptacle Kit, Wire-to-Wire, Solder Type, 6 Circuits	542800609

Downloaded from Arrow.com.