



Combination Pliers

Wire Strippers and Dismantling Tools

Gripping Pliers

Grip Pliers

Circlip Pliers

Carpenters' Pincers

Concreters' Nippers

Cutting Pliers

Pipe Wrenches and Water Pump Pliers

Cycle Pliers

Hose Clamp Pliers

KNIPEX Alligator®

KNIPEX Alligator® XL

KNIPEX Cobra®

KNIPEX Cobra® ES

KNIPEX Cobra® QuickSet

KNIPEX Cobra® XL/XXL

KNIPEX Raptor™ Pliers

Mini-Water Pump Pliers

Pipe and Connector Pliers

Pipe Wrench S-Type

Pipe Wrenches 45°

Pipe Wrenches 90°

Pipe Wrenches S-Type

Pliers for Spring Band Clamps

Pliers Wrench XL

Pliers Wrenches

Self gripping auto adjust pliers

Special Pliers and Tool Lamp

Precision Tweezers

Cable and Wire Rope Shears

Crimping Pliers

Crimp Assortments

Cable Connectors

Insulated Tools

Tools with tethering

Control Cabinet Keys

Tool Kits

Tool Bags / Cases

Sales Aids

spare parts

Symbols

[Products](#) > [Pipe Wrenches and Water Pump Pliers](#) > [KNIPEX Cobra®](#)



87 01 125 KNIPEX Cobra®

High-Tech Water Pump Pliers



Technical details

Description

Special

Applications

Video

	No.	87 01 125
	Pliers	grey atramentized
	Head	polished
	Handles	with non-slip plastic coating
	adjustment positions	13
	Capacity for pipes, inches (diameter)	1 Ø Inch
	Capacities for pipes	1 1/16 Ø Inch 27 Ø mm
	Capacities for nuts	1 1/16 Inch 27 mm
	Length	5 Inch 125 mm
	Net weight	0,187 lbs 85 g

technical change and errors excepted



Products

Cable and Wire Rope Shears
Cable Connectors
Carpenters' Pincers
Circlip Pliers
Combination Pliers
Concreters' Nippers
Control Cabinet Keys
Crimp Assortments
Crimping Pliers
Cutting Pliers
Grip Pliers
Gripping Pliers
Insulated Tools
Pipe Wrenches and Water Pump
Pliers
Precision Tweezers
Sales Aids
spare parts
Special Pliers and Tool Lamp
Tool Bags / Cases

Pliers-ABC

Basic Information about Pliers
Making Combination Pliers

Contact & Service

Contact
Tell Us About Our Tools!
Testimonials

Media Center

News Room
Product Videos
Awards / Contests

About us

KNIPEX in Germany
History
Quality in every detail
Visit us...