



**Part Number :** [731000103](#)  
**Product Description :** SMB Jack, Right-Angle, PCB  
Receptacle, Through Hole, Brass Body, Gold (Au)  
Plated, 80 Pieces Per Tray, 50 Ohms  
**Series Number :** 73404  
**Status :** Active  
**Product Category :** RF / Coaxial Connectors




Documents & Resources

**Drawings**  
[731000103 sd.pdf](#)  
[895420089-000.pdf](#)  
**3D Models and Design Files**  
[731000103 stp.zip](#)  
**Specifications**  
[PS-73598-0099-001.pdf](#)

Product Environment Compliance..

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents



- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	RF / Coaxial Connectors
Series	73404
Description	SMB Jack, Right-Angle, PCB Receptacle, Through Hole, Brass Body, Gold (Au) Plated, 80 Pieces Per Tray, 50 Ohms
Product Name	SMB
Style	PCB
Type	Subminiature
UPC	800753686359

### Electrical

Frequency	6 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 335 Vrms@Sea Level

### Physical

Cable Attachment	N/A
Gender	Jack
Keying to Mating Part	N/A
Net Weight	3.695/g
Orientation	Right Angle
Packaging Type	Tray



Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	Through Hole
PCB Thickness - Recommended	2.40mm
Reverse Polar	No
Wire/Cable Type	N/A

**Solder Process Data**

Max-Duration	10
Lead-Free Process Capability	SMC&WAVE
Max-Cycle	2
Max-Temp	260

---

This document was generated on May 13, 2025