



REV.	DATE	DESCRIPTION
A	12/29/00	REVISE PLATING TO SILVER
B	12/06/06	UPDATE DRAWING FORMAT
C	09/20/07	MODIFY BODY TO HEX COUPLING NUT



RECOMMENDED CABLE
STRIPPING DIM'S

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”	APPROVALS	DATE	Amphenol Connex					
8						DRAWN	G.R.S.						09/20/07
7						CHECKED			PART DESCRIPTION 7/16 PLUG – .250” SEMI RIGID CABLE				
6						ISSUED							
5						SHEET	1 OF 1		PART NO. 272110				
4													
3	CONTACT PIN	BER. COPPER	SILVER	1	DO NOT SCALE DRAWING				DWG. NO. 272110.DWG				
2	INSULATOR	TEFLON	NATURAL	1		C:/272/272110.DWG							
1	BODY	BRASS	NEXCOTE	1					REV. C	SIZE A	SCALE NA		
	DESCRIPTION	MATERIAL	FINISH	QTY									