



ELECTRONICS, INC.
44 FARRAND STREET
BLOOMFIELD, NJ 07003
(973) 748-5089
<http://www.nteinc.com>

NTE3078 & NTE3079

0.56" Single Digit Numeric Display Seven Segment, RHDP

Description:

The NTE3078 (Common Anode) and NTE3079 (Common Cathode) are 0.56 inch (14.2mm) height single digit displays utilizing LED chips which are made from GaAsP on a GaAs substrate.

Features:

- 0.56 Inch (14.2mm) Digit Height
- Low Power Requirement
- Excellent Characters Appearance
- Catagorized for Luminous Intensity
- IC Compatible
- Easy Mounting on PC Board or Socket

Absolute Maximum Ratings: ($T_A = +25^\circ\text{C}$ unless otherwise specified)


Power Dissipation (Per Segment), P_T 100mW
Peak Forward Current (Per Segment, 1/10 Duty Cycle, 0.1ms Pulse Width), $I_{F\text{peak}}$ 100mA
Continuous Forward Current (Per Segment), I_F 40mA
Derate Linearly from 50°C (Per Segment) $0.40\text{mA}/^\circ\text{C}$
Reverse Voltage (Per Segment), V_R 5V
Operating Temperature Range, T_{opr} -40° to $+80^\circ\text{C}$
Storage Temperature Range, T_{stg} -40° to $+85^\circ\text{C}$
Lead Temperatue (During Solder, 1/16" Below Seating Plane, 3sec max), T_L $+260^\circ\text{C}$

Electrical/Optical Characteristics: ($T_A = +25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Average Luminous Intensity: NTE3078 NTE3079	I_V	$I_F = 20\text{mA}$	12	18	32	mcd
	I_V	$I_F = 20\text{mA}$	7	12	18	mcd
Peak Emission Wavelength	λ_P	$I_F = 20\text{mA}$	640	644	650	nm
Spectral Line Half-Width	$\Delta\lambda$	$I_F = 20\text{mA}$	19	24	29	nm
Forward Voltage, Any Segment or D.P.	V_F	$I_F = 20\text{mA}$	1.6	1.85	2.4	V
Reverse Current, Any Segment or D.P.	I_R	$V_R = 5\text{V}$	-	-	100	μA

Pin Connection Diagram

NTE3078



NTE3079

