








NOTES:

1-Material:Phosphor bronze,thickness 0.20
2-Finish on contact area:see table
finish on termination:bright tin over nickel
3-Wire range:20 to 24 AWG
4-Max outer dia of wire insulator:1.73 mm
5-Current carrying capacity per contact:
5.Amps max when crimped to #20 AWG
5 Amps max when crimped to #22 AWG
3 Amps max when crimped to #24 AWG
6-After 5 insertions into connector,
contact retention must be 5 pounds axial load min
7-When contact is crimped to 20 AWG,the insulation
support crimped height must be 1.78 mm max to ensure
a proper insertion into housing
8-Reel should be continous without any contacts
missing in between
9-Packaging:Reel of 400 contacts

NOTE : ROHS INFORMATIONS
The LF products meet European union directives and other country regulations as described in GS-22-008
Terminations plating spec : 2um Nickel min + 2um Sn min
Packaging Spec : see GS-14-920

PULL PART	
86563005067LF	0.4µ Au / GXT
86563005067	0.4µ Au / GXT
86563005065LF	0.75µ Au / GXT
86563005065	0.75µ Au / GXT
PART NUMBER	Plating

rev	ecn no	dr	date
C	LS06-196	MPE	27/11/2006
D	LS08-0127	MPE	2008/05/13
E	110-0070	AMR	2010-03-09
F	111-0003	AMR	2011-01-06
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com

surface - ISO 1302

tolerance std ISO 406 ISO 1101

TOLERANCES UNLESS OTHERWISE SPECIFIED

projection

mm

Dr	C JARRY	28/01/97	ANGULAR	LINEAR	0.X	±0.3	size A3	Scale 10:1
Eng					0.XX	±0.1		
Chr			0°	±2°	0.XXX	±0.05	ECN	111-0003
Appr			Product family			D-SUB	Spec ref	

title: CRIMP PIN
#Wire 20-24 Ø1.52 max

dwg no: C01-8656-1531

Rev. F

catalog no -

CUSTOMER

sheet 1 of 1

Copyright FCI.

REV F - 2006-04-17

Downloaded from Arrow.com.

PDM: Rev:F STATUS:Released Printed: Mar 05, 2011