Part Number : 1200660689
Product Description : M12 Signal, A-Coded, Double-Ended Cordset, 4 Poles, Female (Straight) to Male (Straight), 22 AWG, Yellow TPE Cable, 2.0m (6.56') Length
Series Number : 120066
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Part Number : 884030K05M020

Documents and Resources

Drawings

1200660689_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025) SCIP:333b2313-c211-4107-a6c1-672cd38e190e
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

Downloaded from Arrow.com.

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120066
Description	M12 Signal, A-Coded, Double-Ended Cordset, 4 Poles, Female (Straight) to Male (Straight), 22 AWG, Yellow TPE Cable, 2.0m (6.56') Length
IP Rating	IP67
Product Name	M12 Signal,Micro-Change (M12)
Type	Double Ended
UPC	78172553050

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V

Physical

Cable Diameter	5.20mm (.205")
Cable Length	2.0m (6.56')

Downloaded from Arrow.com.

Color - Cable Jacket	Yellow
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
Coupling Style	Threaded
Gender	Female-Male
Keyway	A-Coded
LED Indicator	None
Material - Cable Jacket	TPE
Material - Connector Body	TPU
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass with Teflon Coat
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	105.300/g
Orientation	Straight to Straight
Poles	4
Temperature Range - Operating	-25° to +85°C
Wire/Cable Type	PLTC/ITC
Wire Size (AWG)	22

Downloaded from Arrow.com.