Part Number : 1212070358
Product Description : mPm DIN Valve Connector, Form A-18mm, External Threads, 2 Pole Plus Ground with C4 Circuit, 24V, Red LED + VDR, Transparent, Integrated Nitrile Gasket, Bulk Pack, Mounted
Series Number : 121207
Status : Active
Product Category : Circular Industrial Connectors
Engineering Part Number : S28200TC422RSN



Documents and Resources

Drawings

1212070358_sd.pdf

Specifications

PK-121207-S28-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

Downloaded from Arrow.com.

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	121207
Description	mPm DIN Valve Connector, Form A-18mm, External Threads, 2 Pole Plus Ground with C4 Circuit, 24V, Red LED + VDR, Transparent, Integrated Nitrile Gasket, Bulk Pack, Mounted
IP Rating	IP67
Product Name	mPm
Type	Field Attachable Connector
UPC	884982505438

Electrical

Current - Maximum per Contact	16.0A
Voltage - Maximum	24V

Physical

Cable Diameter	4.00-9.00mm (.157-.354")
Coupling Type	External Thread
Diagnostics / LEDs	Yes
Diagnostics Port	No
Form	A - 18mm

Downloaded from Arrow.com.

Gender	N/A
Keyway	None
Material - Connector Body	Polyamide
Material - Contact	Brass
Material - Coupling Nut	N/A
Material - Plating Mating	Silver
Net Weight	18.000/g
Orientation	90° Angle
Pitch - Mating Interface	18.00mm
Poles	2
Temperature Range - Operating	-40° to +90°C
Wire Size (AWG)	16

Downloaded from Arrow.com.