





REV.	DATE	DESCRIPTION
NC	03/31/05	INITIAL RELEASE
A	02/23/06	MODIFY FERRULE DIAMETERS



NOTE:

1. CRIMPED FERRULE
HEX CRIMP SIZE .429"
2. CRIMPED CONTACT PI
HEX CRIMP SIZE .118"

Amphenol Connex

N CRIMP PLUG - FOR LMR 400,
(FOR LMR400, B9913 CABLE)

Amphenol Connex									
N CRIMP PLUG – FOR LMR 400, (FOR LMR400, B9913 CABLE)									
172102H243-11									
DWG. NO.		172102H243-11.DWG		REV.	A	SIZE	A	SCALE	NA
PART NO.									
SHEET 1 OF 1									
PART DESCRIPTION									
ISSUED									
CHECKED									
DRAWN G.R.S.									
DATE 02/23/06									
APPROVALS									
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.									
UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm									
UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 ± 0.007" .315 – 1.180 ± 0.015" 1.180 – 4.724 ± 0.020"									
DO NOT SCALE DRAWING									
CADD FILE C:/172/172102H243-11.DWG									
DESCRIPTION									
MATERIAL									
FINISH									
QTY									
FERRULE									
CONTACT PIN									
RETAINER RING									
GASKET									
INSULATOR									
SHELL/BODY									
DESCRIPTION									