



PRODUCT NUMBER	PITCH
KExx74x200J0G	5.00 mm




N=Number of poles
 $\text{Dim L} = N/2 \times 5.0$
 $\text{Dim B} = (N/2 - 1) \times 5.0$
 $\text{Dim C} = (N/2 - 1) \times 5.0$
 $\text{Dim D} = (N/2 - 1) \times 5.0$


Poles	Tolerance
2x2P-2x6P	± 0.15
2x7P-2x12P	± 0.25
2x13P-2x18P	± 0.35
2x19P-2x24P	± 0.40

PART NO.: KE xx 7 4 x 2 00J0 G

Solid block	No. of poles	Color	RoHS compliant (lead<4%) In copper Alloy
0	2	Black (RAL9005)	
04	2x2poles	Red (RAL3001/D)	
06	2x3poles	Orange(RAL2011/P)	
...	...	Yellow(RAL1018/A)	
48	2x24poles	Green(RAL6018/T)	
6		Blue (RAL5015/A)	
8		Grey(RAL7035/D)	
9		White(RAL1102)	
C		Green(RAL6018/U)	



SECTION P-P



RECOMMENDED P.C.B LAYOUT
TOP VIEW

Material:

- Item (a) Terminal(housing): Thermoplastic (UL94 V-0)
- Item (b) Terminal(cover): Thermoplastic (UL94 V-0)
- Item (c) Pin : Copper Tin plated

Electrical:

- Voltage rating: 300V
- Current rating: 12A
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C $\pm$ 5°C/5 Sec
- Safety Approval: cULus

mat'l. code				surface ASME Y14.5		tolerance ASME Y14.5		projection 		product family TERMINAL BLOCK					
ltr	ecn	no	dr	date	tolerances unless otherwise specified						title TERMINAL BLOCK PLUGGABLE SOCKET, OPEN VERTICAL				
					angles 	X.±0.5									
						X.X±0.3									
						X'±1"									
					dr	EVIN ZHONG	042414			dwg no		sheet 1 of 1		size	
				enrg	EVIN ZHONG	042414	KExx74x200J0G			A4					
				chr	HANKE FENG	042414									
				appd	SHI JUN	042414									
sheet index		revision sheet		A	1					type		CUSTOMER Drawing			