



**Part Number :** [2122100020](#)  
**Product Description :** CP-3.3 Header, 3.30mm Pitch, Dual Row, Vertical, Polarized, Positive Lock, Glow-Wire Capable, 2 Circuits, with Potting Capability, Natural  
**Series Number :** 212210  
**Status :** Active  
**Product Category :** PCB Headers and Receptacles



## Documents & Resources

**Drawings**  
[2122100020\\_sd.pdf](#)

**3D Models and Design Files**  
[2122100020\\_stp.zip](#)

**Specifications**  
[2122109200-SPK-200.pdf](#)  
[2122090000-PS-000.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

- Multiple Part Product Compliance Statements
- Eu RoHS
  - REACH SVHC
  - Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	PCB Headers and Receptacles
Series	212210
Description	CP-3.3 Header, 3.30mm Pitch, Dual Row, Vertical, Polarized, Positive Lock, Glow-Wire Capable, 2 Circuits, with Potting Capability, Natural
Application	Power, Wire-to-Board
Component Type	PCB Header
Product Name	CP-3.3
UPC	193264099696

#### Agency

UL	E29179
----	--------

#### Electrical

Current - Maximum per Contact	8.5A
Voltage - Maximum	500V AC/DC

#### Physical

Breakaway	No
Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Natural
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	Yes

Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Matte Tin
Material - Plating Termination	Matte Tin
Material - Resin	Polyamide
Net Weight	751.470/mg
Number of Rows	2
Orientation	Vertical
Packaging Type	Tray
PC Tail Length	3.35mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	3.30mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
CP-3.3 Dual Row Receptacle Housings	<u>212209</u>

---

This document was generated on Jan 15, 2025