


SMD Power Inductor CDEIR18D88ME



Description

- Metal alloy core construction.
- Magnetically shielded.
- L × W × H: 20.0 × 18.7 × 9.4mm Max.
- Product weight : 14.9 g(Ref.)
- Moisture Sensitivity Level: 1
- RoHS compliance.

Environmental Data

- Operating temperature range: -40°C~+125°C (including coil's self temperature rise)
- Storage temperature range: -40°C~+105°C
- Solder reflow temperature: 260 °C peak.


Packaging

- Carrier tape and reel packaging.
- 13.0" diameter reel
- 150pcs per reel

Applications



- Ideally used in Notebook, PDA, Communication equipment and other high current application .

Dimension - [mm]



Dimension Inductance	A (Length)	B (Height)
2.6~3.3 μ H	19.0 $\pm$ 1.0	9.0 $\pm$ 0.4
4.5~10.0 μ H	18.3 $\pm$ 1.0	8.8 $\pm$ 0.4

Land pattern and Schematics - [mm]



SMD Power Inductor CDEIR18D88ME



Electrical Characteristics

Part No.	Stamp	Inductance (μ H) [Within] ※1	D.C.R. (m Ω) Max.(Typ.) (at 20°C)	Saturation Current 1 (A) Typ. (at 20°C) ※2	Saturation Current 2 (A) Typ. (at 20°C) ※3	Temperature Rise Current (A) Typ. ※4
CDEIR18D88MENP-2R6MC	2R6	2.6 $\pm$ 20%	1.9 (1.6)	30.0	45.0	28.0
CDEIR18D88MENP-3R3MC	3R3	3.3 $\pm$ 20%	2.4 (2.0)	30.0	45.0	25.0
CDEIR18D88MENP-4R5MC	4R5	4.5 $\pm$ 20%	3.5 (2.9)	28.0	40.0	21.0
CDEIR18D88MENP-5R6MC	5R6	5.6 $\pm$ 20%	4.0 (3.3)	25.0	38.0	19.0
CDEIR18D88MENP-6R8MC	6R8	6.8 $\pm$ 20%	4.0 (3.3)	19.0	28.0	19.0
CDEIR18D88MENP-100MC	100	10.0 $\pm$ 20%	7.0 (5.8)	15.0	22.0	15.0

※1 Measuring condition at 100kHz 1V.







※2 Saturation current: The actual value of DC current when the inductance decreases to 82% of its nominal value.

※3 Saturation current: The actual value of DC current when the inductance decreases to 70% of its nominal value.

※4 Temperature rise current: The actual value of DC current when the temperature rise is $\Delta T=50^{\circ}\text{C}$ ($T_a=20^{\circ}\text{C}$).

Saturation Current & Temperature Rise Graph



— L (20°C) — ΔT



SMD Power Inductor CDEIR18D88ME



Solder Reflow Condition



Please refer to the sales offices on our website - <http://www.sumida.com>

Hong Kong

Tel. +852-2880-6781
FAX. +852-2565-9600
sales@hk.sumida.com

Saitama(Japan)

Tel. +81-48-691-7300
FAX. +81-48-691-7340
sales@jp.sumida.com

Chicago

Tel. +1-847-545-6700
FAX. +1-847-545-6720
sales@us.sumida.com

Shanghai

Tel. +86-21-5836-3299
FAX. +86-21-5836-3266
shanghai.sales@cn.sumida.com

Seoul

Tel. +82-2-6237-0777
FAX. +82-2-6237-0778
sales@kr.sumida.com

Obernzell

Tel. +49-8591-937-0
FAX. +49-8591-937-103
contact@eu.sumida.com

Shenzhen

Tel. +86-755-8291-0228
FAX. +86-755-8291-0338
shenzhen.sales@cn.sumida.com

Singapore

Tel. +65-6296-3388
FAX. +65-6841-4426
sales@sg.sumida.com

Neumarkt

Tel. +49-9181-4509-110
FAX. +49-9181-4509-310
infocomp@eu.sumida.com

Taipei

Tel. +886-2-8751-2737
FAX. +886-2-8751-2738
sales@tw.sumida.com

San Jose

Tel. +1-408-321-9660
FAX. +1-408-321-9308
sales@us.sumida.com