




LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
F1		ECR-12-003298		13FEB2012	JJ	AC	
G		ECO-15-006810		29DEC2015	LL	SH	
G1		ADD PN -9 WITH TOP 2 LEDS (DUAL COLOR)		10JAN2020	1T	SH	




1. MATERIAL:
HOUSING - PBT POLYESTER, BLACK, UL 94V-0
- TERMINALS - 0.33 THICK PHOS BRONZE PLATED WITH 1.27um MINIMUM THICK HARD GOLD IN LOCALIZED AREA AND 2um MINIMUM THICK MATTE TIN IN ACTION PIN COMPLIANT PIN TERMINAL AREA OVER 1.27um MINIMUM THICK NICKEL UNDERPLATE
- SHIELD - 0.25 THICK COPPER ALLOY PLATED WITH 2.03um MINIMUM BRIGHT TIN OVER 1.27um MINIMUM NICKEL
- GROUNDING CLIP - 2.03 um MIN MATTE TIN OVER COPPER, PRE-PLATED COPPER ALLOY
- LED - DIFUSED EPOXY LENS 2.29 um SILVER OVER NICKEL PRE-PLATED CARBON STEEL LEADS
- ACTION PIN - COMPLIANT PIN CONTACTS 0.3 THICK BRASS PLATED WITH 2um MINIMUM MATTE TIN OVER 1.27um MINIMUM NICKEL UNDERPLAT.
2. JACK CAVITY CONFORMS TO FCC RULES AND REGULATIONS, PART 68 SUBPART F.
3. DRILLED HOLE DIA = 1.020±0.025
COPPER THICKNESS = 0.025±0.075
TIN-LEAD THICKNESS = .008
4. DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER
5. DATE CODE LOCATED ON REAR OF PART APPROXIMATELY AS SHOWN
6. CONTACTS ARE NOT INTENDED TO BE ALIGNED WITH EACH OTHER
7. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
8. ONLY FOR 6368168-7, -8
CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT TECHNICAL REFERENCE GR-1217-CORE ISSUE 1, NOVEMBER 1995.

6368168-1 SHOWN SHEET 1




RECOMMENDED PANEL CUT-OUT



PC BOARD LAYOUT (COMPONENT SIDE)



SHIELD WITH NO LED CUTOUTS AND STANDARD PANEL GROUNDS



OBSOLETE	N/A	GREEN/YELLOW	GREEN/YELLOW	N/A	YES	WITH TOP 2 LED PORTS	6368168-9
	N/A	N/A	N/A	N/A	NO	WITHOUT LED PORTS	6368168-8
	GREEN	GREEN	GREEN	GREEN	NO	WITH LED PORTS	6368168-7
	GREEN	GREEN	YELLOW	YELLOW	YES	WITH LED PORTS	6368168-6
	GREEN	GREEN	GREEN	GREEN	YES	WITH LED PORTS	6368168-5
	YELLOW	YELLOW	GREEN	GREEN	YES	WITH LED PORTS	6368168-4
	N/A	N/A	N/A	N/A	YES	WITHOUT LED PORTS	6368168-2
	N/A	N/A	N/A	N/A	NO	WITHOUT LED PORTS	6368168-1
	LED #4	LED #3	LED #2	LED #1	GROUNDING CLIP	SHIELD STYLE	PART NUMBER



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. FERNANDEZ CHK J. WESTMAN APVD S. FLICKINGER	28 JUL 2005 28 JUL 2005 28 JUL 2005	NAME STACKED MODULAR JACK ASSEMBLY, 2X1, 8 POSITION, SHIELDED PANEL GROUND, OFFSET, CAT 5	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC 108-1854	APPLICATION SPEC 114-2160	SIZE A1	RESTRICTED TO
MATERIAL SEE NOTE 1	FINISH SEE NOTE 1	WEIGHT -	CAGE CODE 00779	DRAWING NO 6368168	REV G1
CUSTOMER DRAWING		SCALE 3:1	SHEET 1	OF 2	

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AA	00	-					
		-	SEE SHEET 1		-	-	-





6368168-6 AS SHOWN

SHIELD WITH LED CUTOUTS AND
STANDARD PANEL GROUNDS



6368168-6 3D VIEW



6368168-9 AS SHOWN
UNMARKED DIMENSIONS SAME
AS 6368168-1

6368168-9
LED CURRENT DIAGRAM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. FERNANDEZ-DOCK 28 JUL 2005	TE Connectivity	
DIMENSIONS:		CHK J. WESTMAN 28 JUL 2005		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD S. FLICKINGER 28 JUL 2005	NAME STACKED MODULAR JACK ASSEMBLY, 2XL, 8 POSITION, SHIELDED PANEL GROUND, OFFSET, CAT 5	
	0 PLC ± 1 PLC ± 2 PLC ±0.1 3 PLC ±0.13 4 PLC ± ANGLES ± FINISH	PRODUCT SPEC 108-1854 APPLICATION SPEC 114-2160 WEIGHT	SIZE A1	
MATERIAL SEE NOTE 1	SEE NOTE 1	CAGE CODE 00779	DRAWING NO. 6368168	RESTRICTED TO G1
CUSTOMER DRAWING		SCALE 3:1	SHEET 2	OF 2