

High Frequency Ceramic Solutions

5.4 GHz Band Pass Filter

P/N 5425BP15A1050

Detail Specification: 5/10/2012

Page 1 of 2

General Specifications


Part Number	5425BP15A1050
Frequency (MHz)	4900 ~ 5950
Attenuation (min.)	40 dB @ 1280 ~ 3300MHz
Attenuation (min.)	25 dB @ 3300 ~ 4000MHz
Attenuation (min.)	7 dB @ 4375 ~ 4465MHz
Attenuation (min.)	14 dB @ 7300 ~ 8930MHz
Attenuation (min.)	25 dB @ 9800 ~ 11900MHz
Insertion Loss	2.0 dB max.
Return Loss	9.0 dB min.

Impedance	50 Ω
Input Power	2W max.
Reel Quantity	4,000
Operating Temperature	-40 to +85°C
Storage Temperature*	-40 to +85°C
Recommended Storage Conditions*	+5 ~ +35°C, Humidity: 45~75%RH

*18 months in vacuum sealed bag and 1 week after opened. Go to: www.johansontechnology.com/silverleads for details


P/N Suffix	Packaging Style	Bulk (loose)	Suffix = S	Eg. 5425BP15A1050S
		T&R (4000pcs)	Suffix = E	Eg. 5425BP15A1050E
	Evaluation Board	5425BP15A1050-EB1SMA		

Terminal Configuration	
No.	Function
1	GND
2	OUT
3	GND
4	IN




Mechanical Dimensions

	In	mm
L	0.079 $\pm$ 0.006	2.00 $\pm$ 0.15
W	0.049 $\pm$ 0.004	1.25 $\pm$ 0.10
T	0.037 $\pm$ 0.004	0.95 $\pm$ 0.10
a	0.051 $\pm$ 0.006	1.30 $\pm$ 0.15
b	0.012 $\pm$ 0.006	0.30 $\pm$ 0.15
c	0.010 $\pm$ 0.006	0.25 $\pm$ 0.15
d	0.014 $\pm$ 0.006	0.35 $\pm$ 0.15



Mounting Considerations

* Line width should be designed to provide 50 ohm impedance, depending on PCB material and thickness  Units: mm

Johanson Technology, Inc. reserves the right to make design changes without notice.
All sales are subject to Johanson Technology, Inc. terms and conditions.



www.johansontechnology.com

4001 Calle Tecate • Camarillo, CA 93012 • TEL 805.389.1166 FAX 805.389.1821

2012 Johanson Technology, Inc. All Rights Reserved

High Frequency Ceramic Solutions



5.4 GHz Band Pass Filter

P/N 5425BP15A1050


Detail Specification: 5/10/2012

Page 2 of 2

Typical Electrical Performance (T=25°C)



Solder Paste recommendation:
SAC 305 type is recommended.



Johanson Technology, Inc. reserves the right to make design changes without notice.
All sales are subject to Johanson Technology, Inc. terms and conditions.



www.johansontechnology.com

101 Calle Tecate • Camarillo, CA 93012 • TEL 805.389.1166 FAX 805.389.1821

2012 Johanson Technology, Inc. All Rights Reserved