




LOC 	DIST -	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			W3	REVIDES PER ECR-17-004272	29MAR17	ST	TD



SCALE 2:1



- 1 BLOCCHETTO ADATTO PER TERMINALI FEMMINA
PER LA SERIE 6.3 mm FASTON
CON RANGO FILO DA 0.8-2.5 MM2.
(SUITABLE FOR RECEPTACLE TERMINALS
WITH WIRE RANGE 0.8-2.5 mm2).
- 2 BAVA ACCETTABILE: 0.3 MAX
(FLASH PERMISSIBLE: 0.3 MAX.)
- 3 SPECIFICA DI PRODOTTO: 108-20035
(PRODUCT SPEC.: 108-20035)
- 4 NON ANCORA RILASCIATO IN PRODUZIONE
(NOT YET RELEASED FOR PRODUCTION)

1,2,3	NATURALE (NATURAL)	PA 6 UNFILLED, UL 94-V2 IEC 60335-1, GW 750°C NO FLAME	280232-8	W
1,2,3	NATURALE (NATURAL)	PA 6.6 UL 94-V0 (PA 6.6 UL 94-V0 UNFILLED)	280232-6	U
1,2,3	NERO (BLACK)	PA 6.6 (PA 6.6 UNFILLED)	280232-5	U
1,2,3	ROSSO (RED)		280232-1	U
1,2,3	NATURALE (NATURAL)		280232	U
NOTE	COLORE (COLOUR)	MATERIALE (MATERIAL)	PART NUMBER	REV

DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	DWN H. YAALI 29OCT2004	TE Connectivity	
		0 PLC ± 1 PLC ±0.3 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±2°	CHK G. TURCO APVD - PRODUCT SPEC SEE NOTE 3 APPLICATION SPEC - WEIGHT -		
MATERIAL SEE TABLE		FINISH -	CUSTOMER DRAWING	NAME POST INSULATION FOR FASTON 6.3 mm series RECEPTACLE CONTACT	
				SIZE A3	CAGE CODE 00779
				DRAWING NO C=280232	RESTRICTED TO -
				SCALE 3:1	SHEET 1
				OF 1	REV W3