



**Part Number :** [1600775006](#)  
**Series Number :** 160077  
**Status :** Active - Proprietary  
**Product Category :** Connector Housings



---

## Drawings

[1600775006\\_sd.pdf](#)  
[PK-31300-635-001.pdf](#)  
[PK-31300-903-001.pdf](#)


## Specifications

[1601110001-AS-000.pdf](#)  
[1600760001-PS-000.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

Status	Active - Proprietary
Category	Connector Housings
Series	160077
Description	MX150 Hybrid Mat-Sealed Male Connector Assembly, Dual Row, 10 Circuits, Keying Option A, Positions 9 and 10 Blocked, Black
Application	Power, Wire-to-Wire, Automotive
Product Name	MX150
UPC	193264669639

### Physical

Circuits (maximum)	10
Color - Resin	Black
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	21.515/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarization	A
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
MX150 Hybrid Sealed, Dual Row, Female Connector Assemblies	<u>160076</u>

### Use with Part(s)

Description	Part Number
MX150 Male Terminals	<u>33000</u>
MX150 Male Terminals	<u>33011</u>
Use With	Industry Standard Terminal 2.80mm

---

This document was generated on May 27, 2026