



**Features**

- High performance magnetics for pulse absorption ( 20dB attenuation at 1,000V pulse ).
- High insertion loss characteristics.


**Applications**

- PCs, Copiers, Printers, Office appliances, Measuring devices and Control systems.

SUP-E□H-EP Series (PVC wire)  
(1~3A)




**Dimensions**




Model Number	A	B	C	D	E	F	H	M	N
SUP-E1H-EP									
SUP-E2H-EP	60	30	80	15	7.0	70	25	20	3
SUP-E3H-EP		40		20				25	4

**Circuit**



**Static characteristics (Representative example)**




Safety Standard	File No.
UL :UL-1283	E78644
CSA :C22.2, No.8-M1986	LR60681
SEMKO :EN60939	SE/0142-13 SE/0142-14

The "ENEC" mark is a common European product certification mark based on testing to harmonised European safety standard.  
\*File No. may be revised without notice. Please contact us at the time of your request for certifications.


SUP-E□H-EP Series (Screw terminal)  
(5~20A)



**Dimensions**



**TVSS Characteristics Pulse width 800nsec**



**Electrical Specifications**

Safety Standard	Model Number	Rated Current (A)	Test Voltage	Insulation Resistance	Leakage Current max.	Voltage Drop max.	Temperature Rise max.	Operating Temperature (°C)	Insertion losses		Weight typ.(g)
									Normal Mode (MHz)	Common Mode (MHz)	
UL, CSA, SEMKO	SUP-E1H-EP	1	Line to Line 1,100Vac 50/60Hz 60sec	Line to Line 3,000MΩmin	1~3A:0.5mA	1.0Vac	30K	-25 ~ +55 (85°C with Temp. rise)	0.7 ~ 30	0.7 ~ 30	105
	SUP-E2H-EP	2									
	SUP-E3H-EP	3									
UL, CSA, SEMKO	SUP-E5H-EP	5	Line to Case 2,240Vac 50/60Hz 60sec	Line to Case 6,000MΩmin (at 500Vdc)	5~20A:0.6mA (at 250Vac 60Hz)	1.0Vac	35K	-25 ~ +50 (85°C with Temp. rise)	0.8 ~ 30	1.5 ~ 30	270
	SUP-E10H-EP	10							1.0 ~ 30	2.0 ~ 30	
	SUP-E15H-EP	15							1.5 ~ 30	6.0 ~ 30	
	SUP-E20H-EP	20									

Guaranteed attenuation is more than 40dB in normal mode, more than 40dB at 1~3A and more than 35dB at 5~20A in common mode.