

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	08MAY2015	DW	CW
	B	ECR-15-013292	24SEP2015	DL	CW
	C	ECR-21-105887	26JUL2021	BS	CW
	D	ECR-22-150866	20SEP2022	DL	CW

NOTES:

1. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 250 V
RATED CURRENT: 10 A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 4 KV
POLLUTION DEGREE: 3
CONTACT RESISTANCE: $\leq 5\text{ m}\Omega$
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: 0.14-2.5 mm² (26-14 AWG)
CONTACT TYPE: CRIMP CONTACT
2. CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING:T20200X20XX000)

注释:

1. 技术参数:
绝缘材料: PC
额定电压: 250V
额定电流: 10A
绝缘电阻: $\geq 400M\Omega$
额定脉冲电压: 4 KV
污染等级: 3
接触电阻: $\leq 5\text{ m}\Omega$
阻燃等级: UL94V-0
插拔次数: 500次
接线范围: 0.14-2.5 mm² (26-14 AWG)
接线类型: 冷压接
2. 端子需要单独订购.
(订货号参考图面: T20200X20XX000)


M4 SCREW
RECOMMENDED
TIGHTENING TORQUE
1.2Nm

PANEL CUT FOR INSERTS FOR USE
WITHOUT HOODS/ HOUSINGS

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC $\pm$
1 PLC $\pm$
2 PLC $\pm$
3 PLC $\pm$
4 PLC $\pm$
ANGLES $\pm$

MATERIAL

-

FINISH

-

DWN 08MAY2015

David Wang

CHK 08MAY2015

Chris Wang

APVD 08MAY2015

Xiang Xu

PRODUCT SPEC

108-137043

APPLICATION SPEC

114-137043

WEIGHT

-

Customer Drawing

HDD-072-F 73-144

T2031442201-000

DESCRIPTION

PART NUMBER



TE Connectivity

NAME

HDD-072-F 73-144

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

T2031442201000

-

SCALE

1:1

SHEET

1 OF 1

REV

D