

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	E	See ECO-19-004147	3/22/19	J.B	T.L

QS1500
Polyolefin, Flexible,
Adhesive Lined,
Heat - Shrinkable Tubing




Table 1: Dimensions mm (inches)

Size	As Supplied		As Recovered							
	Minimum Expanded I.D. Including Core (D)		Maximum Recovered I.D. Including Core (d)		Minimum Recovered Jacket Wall (W2)		Nominal Recovered Adhesive Wall (W1)		Nominal Recovered Total Wall (W)	
	mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.
No. 1	5.72	0.225	1.27	0.050	0.64	0.025	0.56	0.022	1.20	0.047
No. 2	7.62	0.300	1.65	0.065	0.76	0.030	0.76	0.030	1.52	0.060
No. 3	11.55	0.455	2.41	0.095	0.89	0.035	1.02	0.040	1.91	0.075
No. 4	17.78	0.700	4.45	0.175	1.04	0.041	1.37	0.054	2.41	0.095
No. 5	27.94	1.100	7.62	0.300	1.93	0.076	1.57	0.062	3.51	0.138

Material: Fabricated from flame-retarded crosslinked modified flexible polyolefin, with a thermoplastic adhesive liner.

Color: Jacket color is black or red. Adhesive liner shall be amber.

Reference Specification TEC-108-120016

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

© COPYRIGHT 2019 TE Connectivity

DIMENSIONS:	DWN	J. Bitter	12MAR2019	MATERIAL	-	FINISH	-			
INCHES	CHK	Tim Licko	-	 TE Connectivity Ltd.						
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	Tim Licko	-							
0 PLC ± -	PRODUCT SPEC	-	NAME					QS1500		
1 PLC ± -	APPLICATION SPEC	-	Polyolefin, flexible, Adhesive Lined, Heat - shrinkable Tubing							
2 PLC ± -	WEIGHT	-	SIZE	A4	CAGE CODE	06090	DRAWING NO	QS1500	RESTRICTED TO	-
3 PLC ± -	CUSTOMER DRAWING			SCALE	None	SHEET	1 OF 1	REV	E	
4 PLC ± -										
ANGLES ± -										