

5

4

3

2

1

NOTES:

1. MATERIALS AND FINISHES:
N STR PLUG - BRASS, NICKEL PLATING
SMA STR PLUG - BRASS, GOLD PLATING
CABLE - RG 142

2. ELECTRICAL:
A. IMPEDANCE: 50 OHM

3. PACKAGING:
A. QUANTITY: SINGLE PACK
B. MARKING: BAG TO BE MARKED
"AMPHENOL RF, 95-909-195-XXX AND DATE CODE".

REVDESCRIPTIONDATEECNBY

ARELEASE TO MFG.18-JUL-2316722DK

HEAT SHRINK TUBE
TYP(2)

INTERFACE PER
N PLUG

LENGTH 'L' (SEE TABLE)

8.00 MM WRENCH

25.40±1.27
[1.000±0.050]
TYP(2)

INTERFACE PER
MIL-STD-348
SERIES: SMA PLUG

SCALE 0.400

LENGTH TABLE

PART NUMBER (IMPERIAL)	PART NUMBER (METRIC)	LENGTH 'L' IN INCHES [METERS]
95-909-195-006	-	6.00 [0.152]
-	95-909-195M025	9.84 [0.250]
95-909-195-012	-	12.00 [0.305]
95-909-195-018	-	18.00 [0.457]
-	95-909-195M050	19.69 [0.500]
95-909-195-024	-	24.00 [0.610]
95-909-195-036	-	36.00 [0.914]
-	95-909-195M100	39.37 [1.000]
95-909-195-048	-	48.00 [1.219]
-	95-909-195M200	78.74 [2.000]
-	95-909-195M300	118.11 [3.000]

TOLERANCE TABLE

LENGTH IN INCHES/FT [METERS]	TOLERANCE
0" - 23.99" [0 - 0.609]	±0.25" [0.006]
24.00" - 59.99" [0.610 - 1.523]	±0.50" [0.013]
5.0' - 24.99' [1.524 - 7.617]	±2.5%
25.0' & UP [7.620 & UP]	±5.0%

DESIGN REQUIREMENTS

☒ FREQUENCY: DC - 11 GHz

☒ CONTINUITY

☐ VSWR: ____ :1 MAX.

☒ HI-POT: 500 VRMS

☐ INS. LOSS: ____ dB MAX.

☐ OTHER

NOTICE: These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE METRIC [INCHES] AND TOLERANCES ARE:
<0.5mm = ±0.05mm [$<0.020 = \pm0.002$]
0.5 - 6mm = ±0.1mm [$0.020 - 0.236 = \pm0.004$]
>6.00 - 30mm = ±0.2mm [$0.236 - 1.181 = \pm0.008$]
>30.00 - 120mm = ±0.3mm [$>1.181 - 4.725 = \pm0.012$]

ANGLES = ±1°

MATERIAL

SEE NOTES

TITLE

N STR PLUG TO SMA STR PLUG
USING RG 142 CABLE
VARIOUS LENGTH

THIRD ANGLE PROJ.

REFERENCE

ENG.#
11791

ENGR.1
DINESH A

ENGR.2

DATE
20-APR-23

SHEET NO. 2 OF 2

SCALE: 1.8:1.0

SIZE
B

DRAWING NO. 95-909-195-XXX

ITEM NO. 95-909-195-XXX

PART NO. 95-909-195-XXX

REV
A

Amphenol RF

CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

5

4

3

2

1

Downloaded from Arrow.com