


Technical specification:

Rated voltage: IEC 61076-2-101	160 V
Current rating: IEC 61076-2-101	4 A at 40°C
Insulation resistance: IEC 60512	$\geq 100 \text{ M}\Omega$
Pollution degree: IEC 60664-1	3/2
Degree of protection: IEC 60529	IP 67, in mated condition
Temperature range:	-30°C ... +80°C
Mating cycles: IEC 60512-9a	≥ 100

Materials:


Contact:	CuZn
Contact plating:	Nickel, gold plated
Contact carrier:	PBT GF, UL 94
Sealing:	FPM
Counternut:	CuZn, nickel plated
Socket housing:	CuZn, nickel plated

Installation specification:


Recommended torque:	1-1,2 Nm
Conec installation tool:	Torque wrench: 36-000200 Insert across flats 19: 36-000250

Contact assignment:

1	brown
2	white
3	blue
4	black
	shield connection flange housing



Minimum wall thickness 1,5mm,
alternativ panel cut-out d=16,1



D see data sheet cable

Part no:	Description:	Length L:	Cable:
43-02312	SAL - 12S - FKH4 - 0,5 / G2	0,5m	TPU, UL, black, 4x0,25mm ² flexible installation cable: 781-G22400
43-02365	SAL - 12S - FKH4 - 1 / G2	1m	
43-02366	SAL - 12S - FKH4 - 2 / G2	2m	
43-xxxxx	SAL - 12S - FKH4 - ... / G2	x	

DO NOT ALTER CAD DRAWING BY HAND Directive 2002/95/EC RoHS compliant	dim. in mm		title: Female socket M12x1 with cable, backmounting
	date	name	
	drawn	11.09.13	Brüntrup
	appd.	11.09.13	Fromm
tolerance of cable: L ≤ 4m: L + 40mm L > 4m: L + 1%			dwg no: 43K1A2168
general tolerance: 0 ± 0,50mm 0,0 ± 0,25mm 0,00 ± 0,10mm			part no: see table
THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH			

