
FO-55111-C

REV	DOCUMENT	CHANGED BY	CHECK
11	0081896	NMN 21SEP11	CMH

HONEYWELL PART NUMBER

DTV6-2RN4



NOTES

1 - 6X 4-40 UNC X (.125) TERMINAL SCREW AND LOCK WASHER
2 - BUTTON LEVER BRACKET ASSEMBLY MAY BE SET AT ANY POSITION AROUND AXIS OF PLUNGER
3 - SEALED FOR NEMA 1, 3, 4 AND IP 66 RATING

RELEASE NO: PR-11266

CHARACTERISTICS	
OPERATING FORCE	10-30 OZ
RELEASE FORCE	6 OZ MIN
PRETRAVEL	.266 MAX
DIFFERENTIAL TRAVEL	.165 MAX
OVERTRAVEL	.219 MIN
SWITC-BASIC REPLACEMENT	DT-2R3-A7

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

CODE L59 10A - 125 OR 250VAC
0.3A - 125 VDC; 0.15A - 250 VDC

CE 1.5A, 240VAC

DESIGN UNITS: INCH
TOLERANCES UNLESS NOTED:

NO PLACES	X	±	
ONE PLACE	.X	±	.030
TWO PLACE	.XX	±	.015
THREE PLACE	.XXX	±	.005
ANGLES	X	±	0°

THIRD ANGLE PROJECTION

DRAWN	JAP	16JUN82
CHECK	GCH	18JUN82

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.

INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY

RASTER

Honeywell

TITLE
SWITCH - ENCLOSED

SIZE	TYPE	CAGE CODE	DRAWING NAME	REV
B	I	-	DTV6-2RN4	11

SCALE NONE SHEET 1 OF 1

Downloaded from Arrow.com.